

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770335

Luminaire Tested: LD6D70BD010-EU6DR3070959050-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P770335
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR3070959050-6LBCSSQMMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7668.2 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P770335

CATALOG NUMBER: LD6D70BD010-EU6DR3070959050-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P770335

CATALOG NUMBER: LD6D70BD010-EU6DR3070959050-6LBCSSQMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1887346	1887346	1887346
5°	1833163	1831020	1833256
10°	1587797	1576597	1587424
15°	1035959	1030396	1025213
20°	515135	534464	514442
25°	259492	292616	254171
30°	103896	113203	90524
35°	48188	46151	38685
40°	20803	23102	19594
45°	14679	18218	14808
50°	5049	13266	5335
55°	2909	5498	3069
60°	2036	2403	2036
65°	1322	1322	1322
70°	806	537	806
75°	0	355	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 18218 cd/sqm



TEST NUMBER: P770335

CATALOG NUMBER: LD6D70BD010-EU6DR3070959050-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2168.2	28.3
10°-20°	3491.9	45.5
20°-30°	1509.0	19.7
30°-40°	343.9	4.5
40°-50°	118.1	1.5
50°-60°	28.9	0.4
60°-70°	7.5	0.1
70°-80°	0.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7169.1	93.5
0°-40°	7513.0	98.0
0°-60°	7660.0	99.9
0°-90°	7668.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7668.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	24657	24657	24657	24657	24657	
5°	23858	23835	23830	23880	23859	2170
15°	13073	12916	13003	12960	12938	3500
25°	3072	3189	3465	3108	3010	1471
35°	516	527	494	490	414	350
45°	136	168	168	168	137	96
55°	22	23	41	24	23	21
65°	7	7	7	7	7	7
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P770335

CATALOG NUMBER: LD6D70BD010-EU6DR3070959050-6LBCSSQMMMS

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	24657.2	24657.2	24657.2	24657.2	24657.2
2.5°	24493.7	24476.8	24486.5	24498.6	24503.4
5°	23858.2	23835.2	23830.3	23880.0	23859.4
7.5°	22576.2	22543.5	22493.8	22606.4	22711.8
10°	20428.6	20392.3	20284.5	20337.8	20423.8
12.5°	17258.1	17140.6	17138.2	17307.7	17284.7
15°	13073.1	12915.7	13002.9	12960.5	12937.5
17.5°	8791.3	8730.7	8846.9	8811.8	8660.5
20°	6324.1	6339.8	6561.4	6450.0	6315.6
22.5°	4614.7	4671.6	4934.3	4647.4	4542.1
25°	3072.5	3188.7	3464.7	3107.6	3009.5
27.5°	1889.7	1943.0	2222.6	1865.5	1812.2
30°	1175.5	1148.8	1280.8	1099.2	1024.2
32.5°	771.1	737.2	779.6	699.7	639.2
35°	515.7	526.6	493.9	490.3	414.0
37.5°	322.0	370.4	326.9	348.6	266.3
40°	208.2	268.7	231.2	255.4	196.1
42.5°	170.7	207.0	190.1	202.2	174.3
45°	135.6	168.3	168.3	168.3	136.8
47.5°	75.1	112.6	144.1	115.0	79.9
50°	42.4	56.9	111.4	59.3	44.8
52.5°	29.1	32.7	76.3	33.9	30.3
55°	21.8	23.0	41.2	24.2	23.0
57.5°	16.9	18.2	21.8	18.2	16.9
60°	13.3	13.3	15.7	14.5	13.3
62.5°	9.7	9.7	10.9	9.7	9.7
65°	7.3	7.3	7.3	7.3	7.3
67.5°	3.6	4.8	4.8	4.8	4.8
70°	3.6	2.4	2.4	2.4	3.6
72.5°	2.4	1.2	1.2	1.2	1.2
75°	0.0	0.0	1.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)