

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773207

Luminaire Tested: LD6D85BD010-EU6DR6570959040-6LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P773207
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR6570959040-6LBCSSQMB
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9577.5 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P773207

CATALOG NUMBER: LD6D85BD010-EU6DR6570959040-6LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P773207

CATALOG NUMBER: LD6D85BD010-EU6DR6570959040-6LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	507886
5°	506601
10°	506173
15°	490570
20°	446600
25°	389182
30°	323694
35°	256480
40°	185113
45°	116947
50°	60958
55°	32400
60°	17019
65°	9356
70°	3928
75°	4333
80°	2993
85°	2546

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 116947 cd/sqm



TEST NUMBER: P773207

CATALOG NUMBER: LD6D85BD010-EU6DR6570959040-6LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	822.4	8.6
10°-20°	2252.0	23.5
20°-30°	2752.7	28.7
30°-40°	2233.4	23.3
40°-50°	1113.0	11.6
50°-60°	310.4	3.2
60°-70°	70.6	0.7
70°-80°	18.4	0.2
80°-90°	4.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5827.0	60.8
0°-40°	8060.5	84.2
0°-60°	9483.9	99.0
0°-90°	9577.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9577.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8696	
5°	8641	822
15°	8113	2252
25°	6039	2753
35°	3597	2233
45°	1416	1113
55°	318	310
65°	68	71
75°	19	18
85°	4	5
90°	0	



TEST NUMBER: P773207

CATALOG NUMBER: LD6D85BD010-EU6DR6570959040-6LBCSSQMB

CANDELA DISTRIBUTION (FULL):

0°	
0°	8696.1
2.5°	8689.7
5°	8641.1
7.5°	8613.0
10°	8535.1
12.5°	8376.6
15°	8113.4
17.5°	7701.9
20°	7185.6
22.5°	6628.5
25°	6039.3
27.5°	5409.3
30°	4799.8
32.5°	4197.9
35°	3597.3
37.5°	2997.9
40°	2428.0
42.5°	1893.8
45°	1415.9
47.5°	986.5
50°	670.9
52.5°	462.6
55°	318.2
57.5°	214.7
60°	145.7
62.5°	101.0
65°	67.7
67.5°	34.5
70°	23.0
72.5°	21.7
75°	19.2
77.5°	12.8
80°	8.9
82.5°	6.4
85°	3.8
87.5°	2.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)