

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773209

Luminaire Tested: LD6D85BD010-EU6DR6570959040-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P773209
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR6570959040-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9756.1 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P773209

CATALOG NUMBER: LD6D85BD010-EU6DR6570959040-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P773209

CATALOG NUMBER: LD6D85BD010-EU6DR6570959040-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	517365
5°	516058
10°	515620
15°	499724
20°	454935
25°	396451
30°	329736
35°	261264
40°	188566
45°	119128
50°	62094
55°	33001
60°	17334
65°	9535
70°	3996
75°	4400
80°	3061
85°	2613

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 119128 cd/sqm



TEST NUMBER: P773209

CATALOG NUMBER: LD6D85BD010-EU6DR6570959040-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	837.7	8.6
10°-20°	2294.0	23.5
20°-30°	2804.1	28.7
30°-40°	2275.1	23.3
40°-50°	1133.7	11.6
50°-60°	316.2	3.2
60°-70°	71.8	0.7
70°-80°	18.7	0.2
80°-90°	4.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5935.8	60.8
0°-40°	8210.9	84.2
0°-60°	9660.8	99.0
0°-90°	9756.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9756.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8858	
5°	8802	838
15°	8265	2294
25°	6152	2804
35°	3664	2275
45°	1442	1134
55°	324	316
65°	69	72
75°	20	19
85°	4	5
90°	0	



TEST NUMBER: P773209

CATALOG NUMBER: LD6D85BD010-EU6DR6570959040-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	8858.4
2.5°	8851.9
5°	8802.4
7.5°	8773.8
10°	8694.4
12.5°	8532.9
15°	8264.8
17.5°	7845.6
20°	7319.7
22.5°	6752.2
25°	6152.1
27.5°	5510.3
30°	4889.4
32.5°	4276.2
35°	3664.4
37.5°	3053.9
40°	2473.3
42.5°	1929.2
45°	1442.3
47.5°	1004.9
50°	683.4
52.5°	471.2
55°	324.1
57.5°	218.7
60°	148.4
62.5°	102.8
65°	69.0
67.5°	35.1
70°	23.4
72.5°	22.1
75°	19.5
77.5°	13.0
80°	9.1
82.5°	6.5
85°	3.9
87.5°	2.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)