

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P770892

Luminaire Tested: LD6D70BD010-EU6DR6570959050-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P770892
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D70BD010-EU6DR6570959050-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6778.6 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P770892
CATALOG NUMBER: LD6D70BD010-EU6DR6570959050-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P770892

CATALOG NUMBER: LD6D70BD010-EU6DR6570959050-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93		
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87		
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80		
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75		
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69		
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65		
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60		
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57		
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53		
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	729217
5°	729820
10°	755511
15°	756762
20°	696730
25°	593641
30°	454453
35°	321066
40°	189512
45°	76935
50°	27894
55°	15544
60°	8916
65°	4912
70°	5143
75°	4010
80°	4153
85°	3510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 76935 cd/sqm



TEST NUMBER: P770892

CATALOG NUMBER: LD6D70BD010-EU6DR6570959050-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	642.7	9.5
10°-20°	1853.8	27.3
20°-30°	2224.2	32.8
30°-40°	1494.7	22.1
40°-50°	447.4	6.6
50°-60°	79.0	1.2
60°-70°	22.5	0.3
70°-80°	11.0	0.2
80°-90°	3.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4720.6	69.6
0°-40°	6215.3	91.7
0°-60°	6741.7	99.5
0°-90°	6778.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6778.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6674	
5°	6654	643
15°	6690	1854
25°	4924	2224
35°	2407	1495
45°	498	447
55°	82	79
65°	19	22
75°	10	11
85°	3	3
90°	0	



TEST NUMBER: P770892

CATALOG NUMBER: LD6D70BD010-EU6DR6570959050-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6674.1
2.5°	6702.5
5°	6654.2
7.5°	6754.7
10°	6809.7
12.5°	6796.4
15°	6690.2
17.5°	6430.3
20°	5992.2
22.5°	5476.2
25°	4924.2
27.5°	4301.1
30°	3602.1
32.5°	2968.6
35°	2407.1
37.5°	1852.3
40°	1328.7
42.5°	867.8
45°	497.9
47.5°	263.7
50°	164.1
52.5°	113.8
55°	81.6
57.5°	58.8
60°	40.8
62.5°	26.6
65°	19.0
67.5°	17.1
70°	16.1
72.5°	12.3
75°	9.5
77.5°	8.5
80°	6.6
82.5°	4.7
85°	2.8
87.5°	1.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)