

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773296

Luminaire Tested: LD6D85BD010-EU6DR7070959040-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P773296
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR7070959040-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6786.3 lumens
Efficiency: N/A
Efficacy: 77.4 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P773296
CATALOG NUMBER: LD6D85BD010-EU6DR7070959040-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P773296
 CATALOG NUMBER: LD6D85BD010-EU6DR7070959040-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	833627
5°	808854
10°	786310
15°	775992
20°	724624
25°	544370
30°	384824
35°	136317
40°	71671
45°	76347
50°	79057
55°	80539
60°	81050
65°	79318
70°	74881
75°	69359
80°	61537
85°	50020

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 81056 cd/sqm



TEST NUMBER: P773296

CATALOG NUMBER: LD6D85BD010-EU6DR7070959040-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	695.6	10.3
10°-20°	1908.0	28.1
20°-30°	2101.4	31.0
30°-40°	802.9	11.8
40°-50°	379.1	5.6
50°-60°	376.9	5.6
60°-70°	301.7	4.4
70°-80°	173.4	2.6
80°-90°	47.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4705.0	69.3
0°-40°	5507.9	81.2
0°-60°	6263.9	92.3
0°-90°	6786.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6786.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7630	
5°	7375	696
15°	6860	1908
25°	4516	2101
35°	1022	803
45°	494	379
55°	423	377
65°	307	302
75°	164	173
85°	40	47
90°	0	



TEST NUMBER: P773296

CATALOG NUMBER: LD6D85BD010-EU6DR7070959040-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	7629.7
2.5°	7550.0
5°	7374.8
7.5°	7228.7
10°	7087.3
12.5°	6967.7
15°	6860.2
17.5°	6600.5
20°	6232.1
22.5°	5437.2
25°	4515.5
27.5°	3930.8
30°	3050.2
32.5°	1970.2
35°	1022.0
37.5°	552.1
40°	502.5
42.5°	498.9
45°	494.1
47.5°	483.2
50°	465.1
52.5°	444.5
55°	422.8
57.5°	398.6
60°	370.9
62.5°	339.4
65°	306.8
67.5°	270.6
70°	234.4
72.5°	198.1
75°	164.3
77.5°	129.3
80°	97.8
82.5°	68.9
85°	39.9
87.5°	15.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)