

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773414

Luminaire Tested: LD6D90BD010-EU6DR3070959027-6LBSQW1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P773414
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D90BD010-EU6DR3070959027-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8699.0 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P773414

CATALOG NUMBER: LD6D90BD010-EU6DR3070959027-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P773414

CATALOG NUMBER: LD6D90BD010-EU6DR3070959027-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2141034	2141034	2141034
5°	2079568	2077140	2079676
10°	1801220	1788519	1800792
15°	1175206	1168898	1163018
20°	584380	606300	583590
25°	294372	331947	288334
30°	117861	128423	102685
35°	54664	52356	43890
40°	23601	26209	22232
45°	16649	20665	16800
50°	5728	15040	6049
55°	3296	6232	3483
60°	2312	2740	2312
65°	1485	1485	1485
70°	918	604	918
75°	0	414	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°
 Vertical Angle: 45°
 Luminance: 20665 cd/sqm



TEST NUMBER: P773414

CATALOG NUMBER: LD6D90BD010-EU6DR3070959027-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2459.7	28.3
10°-20°	3961.3	45.5
20°-30°	1711.8	19.7
30°-40°	390.2	4.5
40°-50°	134.0	1.5
50°-60°	32.7	0.4
60°-70°	8.5	0.1
70°-80°	0.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8132.8	93.5
0°-40°	8522.9	98.0
0°-60°	8689.6	99.9
0°-90°	8699.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8699.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	27972	27972	27972	27972	27972	
5°	27065	27039	27034	27090	27066	2462
15°	14830	14652	14751	14703	14676	3971
25°	3486	3617	3930	3525	3414	1668
35°	585	597	560	556	470	397
45°	154	191	191	191	155	109
55°	25	26	47	28	26	24
65°	8	8	8	8	8	8
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P773414

CATALOG NUMBER: LD6D90BD010-EU6DR3070959027-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	27971.5	27971.5	27971.5	27971.5	27971.5
2.5°	27786.1	27766.9	27777.9	27791.6	27797.1
5°	27065.1	27039.0	27033.5	27089.8	27066.5
7.5°	25610.8	25573.7	25517.4	25645.1	25764.6
10°	23174.5	23133.3	23011.1	23071.5	23169.0
12.5°	19577.8	19444.6	19441.9	19634.2	19608.1
15°	14830.3	14651.8	14750.7	14702.6	14676.5
17.5°	9972.9	9904.3	10036.1	9996.3	9824.6
20°	7174.2	7192.0	7443.3	7317.0	7164.5
22.5°	5235.0	5299.6	5597.6	5272.1	5152.6
25°	3485.5	3617.3	3930.4	3525.3	3414.0
27.5°	2143.7	2204.2	2521.4	2116.3	2055.8
30°	1333.5	1303.3	1453.0	1247.0	1161.8
32.5°	874.8	836.3	884.4	793.8	725.1
35°	585.0	597.4	560.3	556.2	469.7
37.5°	365.3	420.2	370.8	395.5	302.1
40°	236.2	304.9	262.3	289.8	222.5
42.5°	193.6	234.8	215.6	229.3	197.8
45°	153.8	190.9	190.9	190.9	155.2
47.5°	85.1	127.7	163.4	130.5	90.6
50°	48.1	64.5	126.3	67.3	50.8
52.5°	33.0	37.1	86.5	38.5	34.3
55°	24.7	26.1	46.7	27.5	26.1
57.5°	19.2	20.6	24.7	20.6	19.2
60°	15.1	15.1	17.9	16.5	15.1
62.5°	11.0	11.0	12.4	11.0	11.0
65°	8.2	8.2	8.2	8.2	8.2
67.5°	4.1	5.5	5.5	5.5	5.5
70°	4.1	2.7	2.7	2.7	4.1
72.5°	2.7	1.4	1.4	1.4	1.4
75°	0.0	0.0	1.4	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)