

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773950

Luminaire Tested: LD6D90BD010-EU6DR6570959027-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P773950
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D90BD010-EU6DR6570959027-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9497.6 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P773950

CATALOG NUMBER: LD6D90BD010-EU6DR6570959027-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P773950

CATALOG NUMBER: LD6D90BD010-EU6DR6570959027-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93	93	93	93
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72	72	72	72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56	56	56	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49	49	49	49
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	503652
5°	502380
10°	501950
15°	486476
20°	442877
25°	385940
30°	320996
35°	254341
40°	183573
45°	115972
50°	60449
55°	32125
60°	16879
65°	9287
70°	3893
75°	4287
80°	2993
85°	2546

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 115972 cd/sqm



TEST NUMBER: P773950

CATALOG NUMBER: LD6D90BD010-EU6DR6570959027-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	815.5	8.6
10°-20°	2233.2	23.5
20°-30°	2729.7	28.7
30°-40°	2214.8	23.3
40°-50°	1103.7	11.6
50°-60°	307.8	3.2
60°-70°	70.0	0.7
70°-80°	18.2	0.2
80°-90°	4.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5778.5	60.8
0°-40°	7993.3	84.2
0°-60°	9404.8	99.0
0°-90°	9497.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9497.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8624	
5°	8569	816
15°	8046	2233
25°	5989	2730
35°	3567	2215
45°	1404	1104
55°	316	308
65°	67	70
75°	19	18
85°	4	5
90°	0	



TEST NUMBER: P773950

CATALOG NUMBER: LD6D90BD010-EU6DR6570959027-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	8623.6
2.5°	8617.3
5°	8569.1
7.5°	8541.2
10°	8463.9
12.5°	8306.8
15°	8045.7
17.5°	7637.7
20°	7125.7
22.5°	6573.2
25°	5989.0
27.5°	5364.3
30°	4759.8
32.5°	4162.9
35°	3567.3
37.5°	2973.0
40°	2407.8
42.5°	1878.1
45°	1404.1
47.5°	978.3
50°	665.3
52.5°	458.7
55°	315.5
57.5°	212.9
60°	144.5
62.5°	100.1
65°	67.2
67.5°	34.2
70°	22.8
72.5°	21.5
75°	19.0
77.5°	12.7
80°	8.9
82.5°	6.3
85°	3.8
87.5°	2.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)