

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771636

Luminaire Tested: LD6D75BD010-EU6DR6570959035-6LBCSSQMW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P771636  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D75BD010-EU6DR6570959035-6LBCSSQMW  
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7727.9 lumens  
Efficiency: N/A  
Efficacy: 106.7 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct

Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P771636  
CATALOG NUMBER: LD6D75BD010-EU6DR6570959035-6LBCSSQMW

### Luminous Intensity Polar Plot





TEST NUMBER: P771636

CATALOG NUMBER: LD6D75BD010-EU6DR6570959035-6LBCSSQMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	409802
5°	408765
10°	408421
15°	395828
20°	360352
25°	314024
30°	261178
35°	206949
40°	149363
45°	94365
50°	49183
55°	26138
60°	13725
65°	7545
70°	3176
75°	3498
80°	2422
85°	2077

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 94365 cd/sqm



TEST NUMBER: P771636

CATALOG NUMBER: LD6D75BD010-EU6DR6570959035-6LBCSSQMW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	663.6	8.6
10°-20°	1817.1	23.5
20°-30°	2221.1	28.7
30°-40°	1802.1	23.3
40°-50°	898.0	11.6
50°-60°	250.5	3.2
60°-70°	56.9	0.7
70°-80°	14.8	0.2
80°-90°	3.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4701.7	60.8
0°-40°	6503.8	84.2
0°-60°	7652.3	99.0
0°-90°	7727.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7727.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7017	
5°	6972	664
15°	6546	1817
25°	4873	2221
35°	2903	1802
45°	1142	898
55°	257	250
65°	55	57
75°	16	15
85°	3	4
90°	0	



TEST NUMBER: P771636

CATALOG NUMBER: LD6D75BD010-EU6DR6570959035-6LBCSSQMW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7016.7
2.5°	7011.5
5°	6972.3
7.5°	6949.7
10°	6886.8
12.5°	6758.9
15°	6546.5
17.5°	6214.5
20°	5797.9
22.5°	5348.3
25°	4873.0
27.5°	4364.7
30°	3872.8
32.5°	3387.2
35°	2902.6
37.5°	2419.0
40°	1959.1
42.5°	1528.1
45°	1142.5
47.5°	796.0
50°	541.3
52.5°	373.3
55°	256.7
57.5°	173.2
60°	117.5
62.5°	81.5
65°	54.6
67.5°	27.8
70°	18.6
72.5°	17.5
75°	15.5
77.5°	10.3
80°	7.2
82.5°	5.2
85°	3.1
87.5°	2.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)