

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771723

Luminaire Tested: LD6D75BD010-EU6DR7070959035-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P771723
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D75BD010-EU6DR7070959035-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5375.3 lumens
Efficiency: N/A
Efficacy: 74.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P771723
CATALOG NUMBER: LD6D75BD010-EU6DR7070959035-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P771723
 CATALOG NUMBER: LD6D75BD010-EU6DR7070959035-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	660317
5°	640696
10°	622830
15°	614667
20°	573969
25°	431192
30°	304811
35°	107973
40°	56767
45°	60478
50°	62620
55°	63795
60°	64202
65°	62824
70°	59291
75°	54922
80°	48764
85°	39615

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 64218 cd/sqm



TEST NUMBER: P771723

CATALOG NUMBER: LD6D75BD010-EU6DR7070959035-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	551.0	10.3
10°-20°	1511.3	28.1
20°-30°	1664.5	31.0
30°-40°	636.0	11.8
40°-50°	300.3	5.6
50°-60°	298.5	5.6
60°-70°	239.0	4.4
70°-80°	137.4	2.6
80°-90°	37.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3726.8	69.3
0°-40°	4362.8	81.2
0°-60°	4961.6	92.3
0°-90°	5375.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5375.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6044	
5°	5842	551
15°	5434	1511
25°	3577	1665
35°	810	636
45°	391	300
55°	335	299
65°	243	239
75°	130	137
85°	32	37
90°	0	



TEST NUMBER: P771723

CATALOG NUMBER: LD6D75BD010-EU6DR7070959035-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	6043.5
2.5°	5980.3
5°	5841.6
7.5°	5725.8
10°	5613.8
12.5°	5519.1
15°	5434.0
17.5°	5228.2
20°	4936.4
22.5°	4306.8
25°	3576.7
27.5°	3113.6
30°	2416.0
32.5°	1560.6
35°	809.5
37.5°	437.3
40°	398.0
42.5°	395.2
45°	391.4
47.5°	382.7
50°	368.4
52.5°	352.1
55°	334.9
57.5°	315.8
60°	293.8
62.5°	268.9
65°	243.0
67.5°	214.3
70°	185.6
72.5°	156.9
75°	130.1
77.5°	102.4
80°	77.5
82.5°	54.5
85°	31.6
87.5°	12.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)