

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773466

Luminaire Tested: LD6D90BD010-EU6DR3070959050-6LBSQW1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P773466
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D90BD010-EU6DR3070959050-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9547.4 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P773466
CATALOG NUMBER: LD6D90BD010-EU6DR3070959050-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P773466

CATALOG NUMBER: LD6D90BD010-EU6DR3070959050-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2349844	2349844	2349844
5°	2282384	2279718	2282499
10°	1976892	1962948	1976425
15°	1289824	1282898	1276447
20°	641367	665429	640511
25°	323079	364319	316458
30°	129351	140947	112699
35°	59999	57467	48169
40°	25899	28767	24401
45°	18272	22678	18435
50°	6287	16516	6645
55°	3616	6833	3817
60°	2541	3001	2541
65°	1630	1630	1630
70°	1007	671	1007
75°	0	444	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 22678 cd/sqm



TEST NUMBER: P773466

CATALOG NUMBER: LD6D90BD010-EU6DR3070959050-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2699.6	28.3
10°-20°	4347.7	45.5
20°-30°	1878.7	19.7
30°-40°	428.2	4.5
40°-50°	147.0	1.5
50°-60°	35.9	0.4
60°-70°	9.3	0.1
70°-80°	1.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8925.9	93.5
0°-40°	9354.2	98.0
0°-60°	9537.1	99.9
0°-90°	9547.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9547.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	30700	30700	30700	30700	30700	
5°	29705	29676	29670	29732	29706	2702
15°	16277	16081	16189	16136	16108	4358
25°	3825	3970	4314	3869	3747	1831
35°	642	656	615	610	516	436
45°	169	210	210	210	170	120
55°	27	29	51	30	29	26
65°	9	9	9	9	9	9
75°	0	0	2	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P773466

CATALOG NUMBER: LD6D90BD010-EU6DR3070959050-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	30699.5	30699.5	30699.5	30699.5	30699.5
2.5°	30496.0	30474.9	30487.0	30502.0	30508.1
5°	29704.7	29676.1	29670.0	29731.8	29706.2
7.5°	28108.5	28067.8	28006.0	28146.2	28277.3
10°	25434.7	25389.5	25255.3	25321.6	25428.7
12.5°	21487.2	21341.0	21338.0	21549.0	21520.4
15°	16276.7	16080.8	16189.3	16136.5	16107.9
17.5°	10945.6	10870.2	11014.9	10971.2	10782.8
20°	7873.8	7893.4	8169.2	8030.6	7863.3
22.5°	5745.6	5816.4	6143.5	5786.3	5655.2
25°	3825.4	3970.1	4313.7	3869.1	3747.0
27.5°	2352.8	2419.1	2767.3	2322.7	2256.3
30°	1463.5	1430.4	1594.7	1368.6	1275.1
32.5°	960.1	917.9	970.7	871.2	795.8
35°	642.1	655.6	615.0	610.4	515.5
37.5°	400.9	461.2	407.0	434.1	331.6
40°	259.2	334.6	287.9	318.0	244.2
42.5°	212.5	257.7	236.6	251.7	217.0
45°	168.8	209.5	209.5	209.5	170.3
47.5°	93.4	140.2	179.4	143.2	99.5
50°	52.8	70.8	138.7	73.9	55.8
52.5°	36.2	40.7	95.0	42.2	37.7
55°	27.1	28.6	51.2	30.1	28.6
57.5°	21.1	22.6	27.1	22.6	21.1
60°	16.6	16.6	19.6	18.1	16.6
62.5°	12.1	12.1	13.6	12.1	12.1
65°	9.0	9.0	9.0	9.0	9.0
67.5°	4.5	6.0	6.0	6.0	6.0
70°	4.5	3.0	3.0	3.0	4.5
72.5°	3.0	1.5	1.5	1.5	1.5
75°	0.0	0.0	1.5	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)