

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774012

Luminaire Tested: LD6D90BD010-EU6DR6570959050-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P774012
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D90BD010-EU6DR6570959050-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9167.1 lumens
Efficiency: N/A
Efficacy: 92.7 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P774012
CATALOG NUMBER: LD6D90BD010-EU6DR6570959050-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P774012

CATALOG NUMBER: LD6D90BD010-EU6DR6570959050-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	986144
5°	986960
10°	1021704
15°	1023397
20°	942206
25°	802806
30°	614580
35°	434188
40°	256291
45°	104052
50°	37718
55°	21011
60°	12062
65°	6644
70°	6964
75°	5404
80°	5663
85°	4764

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 104052 cd/sqm



TEST NUMBER: P774012

CATALOG NUMBER: LD6D90BD010-EU6DR6570959050-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	869.1	9.5
10°-20°	2506.9	27.3
20°-30°	3007.8	32.8
30°-40°	2021.3	22.1
40°-50°	605.1	6.6
50°-60°	106.8	1.2
60°-70°	30.4	0.3
70°-80°	14.9	0.2
80°-90°	4.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6383.9	69.6
0°-40°	8405.2	91.7
0°-60°	9117.1	99.5
0°-90°	9167.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9167.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9026	
5°	8999	869
15°	9047	2507
25°	6659	3008
35°	3255	2021
45°	673	605
55°	110	107
65°	26	30
75°	13	15
85°	4	5
90°	0	



TEST NUMBER: P774012

CATALOG NUMBER: LD6D90BD010-EU6DR6570959050-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	9025.6
2.5°	9064.1
5°	8998.7
7.5°	9134.6
10°	9209.0
12.5°	9191.1
15°	9047.4
17.5°	8696.0
20°	8103.4
22.5°	7405.7
25°	6659.2
27.5°	5816.6
30°	4871.3
32.5°	4014.5
35°	3255.2
37.5°	2504.9
40°	1796.9
42.5°	1173.6
45°	673.4
47.5°	356.6
50°	221.9
52.5°	153.9
55°	110.3
57.5°	79.5
60°	55.2
62.5°	35.9
65°	25.7
67.5°	23.1
70°	21.8
72.5°	16.7
75°	12.8
77.5°	11.5
80°	9.0
82.5°	6.4
85°	3.8
87.5°	2.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)