

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P771648

Luminaire Tested: LD6D75BD010-EU6DR6570959040-6LBCSSQMMS

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P771648  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D75BD010-EU6DR6570959040-6LBCSSQMMMS  
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7941.0 lumens  
Efficiency: N/A  
Efficacy: 109.7 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 72.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P771648  
CATALOG NUMBER: LD6D75BD010-EU6DR6570959040-6LBCSSQMMS

### Luminous Intensity Polar Plot





TEST NUMBER: P771648

CATALOG NUMBER: LD6D75BD010-EU6DR6570959040-6LBCSSQMMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	421104
5°	420039
10°	419677
15°	406742
20°	370290
25°	322685
30°	268380
35°	212653
40°	153480
45°	96967
50°	50546
55°	26861
60°	14110
65°	7767
70°	3262
75°	3588
80°	2489
85°	2144

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 96967 cd/sqm



TEST NUMBER: P771648

CATALOG NUMBER: LD6D75BD010-EU6DR6570959040-6LBCSSQMMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	681.9	8.6
10°-20°	1867.2	23.5
20°-30°	2282.3	28.7
30°-40°	1851.8	23.3
40°-50°	922.8	11.6
50°-60°	257.4	3.2
60°-70°	58.5	0.7
70°-80°	15.2	0.2
80°-90°	3.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4831.3	60.8
0°-40°	6683.2	84.2
0°-60°	7863.3	99.0
0°-90°	7941.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7941.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7210	
5°	7165	682
15°	6727	1867
25°	5007	2282
35°	2983	1852
45°	1174	923
55°	264	257
65°	56	59
75°	16	15
85°	3	4
90°	0	



TEST NUMBER: P771648

CATALOG NUMBER: LD6D75BD010-EU6DR6570959040-6LBCSSQMMS

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	7210.2
2.5°	7204.9
5°	7164.6
7.5°	7141.3
10°	7076.6
12.5°	6945.3
15°	6727.0
17.5°	6385.8
20°	5957.8
22.5°	5495.8
25°	5007.4
27.5°	4485.0
30°	3979.6
32.5°	3480.6
35°	2982.6
37.5°	2485.7
40°	2013.1
42.5°	1570.2
45°	1174.0
47.5°	818.0
50°	556.3
52.5°	383.6
55°	263.8
57.5°	178.0
60°	120.8
62.5°	83.7
65°	56.2
67.5°	28.6
70°	19.1
72.5°	18.0
75°	15.9
77.5°	10.6
80°	7.4
82.5°	5.3
85°	3.2
87.5°	2.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)