

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774648

Luminaire Tested: LD6D95BD010-EU6DR6070959024-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P774648
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR6070959024-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7666.6 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P774648
CATALOG NUMBER: LD6D95BD010-EU6DR6070959024-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P774648

CATALOG NUMBER: LD6D95BD010-EU6DR6070959024-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	994830
5°	1019294
10°	1031601
15°	982744
20°	866477
25°	700828
30°	474047
35°	237555
40°	38539
45°	37718
50°	38466
55°	39051
60°	40142
65°	41055
70°	42009
75°	42511
80°	41024
85°	34224

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 42511 cd/sqm



TEST NUMBER: P774648

CATALOG NUMBER: LD6D95BD010-EU6DR6070959024-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	888.2	11.6
10°-20°	2403.1	31.3
20°-30°	2585.6	33.7
30°-40°	1123.9	14.7
40°-50°	188.8	2.5
50°-60°	183.6	2.4
60°-70°	157.0	2.0
70°-80°	105.0	1.4
80°-90°	31.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5876.9	76.7
0°-40°	7000.8	91.3
0°-60°	7373.2	96.2
0°-90°	7666.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7666.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9105	
5°	9294	888
15°	8688	2403
25°	5813	2586
35°	1781	1124
45°	244	189
55°	205	184
65°	159	157
75°	101	105
85°	27	31
90°	0	



TEST NUMBER: P774648

CATALOG NUMBER: LD6D95BD010-EU6DR6070959024-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	9105.1
2.5°	9361.0
5°	9293.5
7.5°	9314.8
10°	9298.2
12.5°	9106.2
15°	8688.0
17.5°	8126.3
20°	7452.1
22.5°	6730.4
25°	5813.3
27.5°	4649.7
30°	3757.4
32.5°	2896.0
35°	1781.0
37.5°	761.9
40°	270.2
42.5°	248.8
45°	244.1
47.5°	235.8
50°	226.3
52.5°	215.7
55°	205.0
57.5°	194.3
60°	183.7
62.5°	171.8
65°	158.8
67.5°	145.7
70°	131.5
72.5°	116.1
75°	100.7
77.5°	82.9
80°	65.2
82.5°	46.2
85°	27.3
87.5°	9.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)