

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774193

Luminaire Tested: LD6D95BD010-EU6DR3070959027-6LBSQW1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774193
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR3070959027-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8047.8 lumens
Efficiency: N/A
Efficacy: 81.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')


CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P774193
CATALOG NUMBER: LD6D95BD010-EU6DR3070959027-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P774193

CATALOG NUMBER: LD6D95BD010-EU6DR3070959027-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96								
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92								
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89								
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85								
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82								
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79								
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77								
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74								
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72								
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1980759	1980759	1980759
5°	1923899	1921655	1923999
10°	1666391	1654639	1665995
15°	1087237	1081397	1075961
20°	540630	560913	539905
25°	272329	307100	266755
30°	109040	118807	94996
35°	50571	48440	40601
40°	21833	24251	20564
45°	15404	19117	15545
50°	5299	13920	5597
55°	3056	5765	3216
60°	2143	2526	2143
65°	1376	1376	1376
70°	850	559	850
75°	0	384	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 19117 cd/sqm



TEST NUMBER: P774193

CATALOG NUMBER: LD6D95BD010-EU6DR3070959027-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2275.5	28.3
10°-20°	3664.8	45.5
20°-30°	1583.7	19.7
30°-40°	361.0	4.5
40°-50°	123.9	1.5
50°-60°	30.3	0.4
60°-70°	7.8	0.1
70°-80°	0.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7524.0	93.5
0°-40°	7884.9	98.0
0°-60°	8039.2	99.9
0°-90°	8047.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8047.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	25878	25878	25878	25878	25878	
5°	25039	25015	25010	25062	25040	2277
15°	13720	13555	13646	13602	13578	3674
25°	3224	3346	3636	3261	3158	1543
35°	541	553	518	515	434	367
45°	142	177	177	177	144	101
55°	23	24	43	25	24	22
65°	8	8	8	8	8	7
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P774193

CATALOG NUMBER: LD6D95BD010-EU6DR3070959027-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	25877.6	25877.6	25877.6	25877.6	25877.6
2.5°	25706.1	25688.3	25698.5	25711.2	25716.3
5°	25039.1	25015.0	25009.9	25062.0	25040.4
7.5°	23693.6	23659.3	23607.2	23725.4	23835.9
10°	21439.8	21401.6	21288.6	21344.5	21434.7
12.5°	18112.3	17989.1	17986.5	18164.4	18140.3
15°	13720.2	13555.0	13646.5	13602.0	13577.9
17.5°	9226.4	9162.9	9284.8	9248.0	9089.2
20°	6637.1	6653.6	6886.1	6769.2	6628.2
22.5°	4843.2	4902.9	5178.6	4877.5	4766.9
25°	3224.5	3346.5	3636.2	3261.4	3158.5
27.5°	1983.3	2039.2	2332.6	1957.8	1901.9
30°	1233.7	1205.7	1344.2	1153.6	1074.8
32.5°	809.3	773.7	818.2	734.4	670.8
35°	541.2	552.7	518.4	514.6	434.5
37.5°	338.0	388.8	343.0	365.9	279.5
40°	218.5	282.1	242.7	268.1	205.8
42.5°	179.1	217.3	199.5	212.2	183.0
45°	142.3	176.6	176.6	176.6	143.6
47.5°	78.8	118.2	151.2	120.7	83.9
50°	44.5	59.7	116.9	62.3	47.0
52.5°	30.5	34.3	80.0	35.6	31.8
55°	22.9	24.1	43.2	25.4	24.1
57.5°	17.8	19.1	22.9	19.1	17.8
60°	14.0	14.0	16.5	15.2	14.0
62.5°	10.2	10.2	11.4	10.2	10.2
65°	7.6	7.6	7.6	7.6	7.6
67.5°	3.8	5.1	5.1	5.1	5.1
70°	3.8	2.5	2.5	2.5	3.8
72.5°	2.5	1.3	1.3	1.3	1.3
75°	0.0	0.0	1.3	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)