

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774662

Luminaire Tested: LD6D95BD010-EU6DR6070959027-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P774662
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR6070959027-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9782.9 lumens
Efficiency: N/A
Efficacy: 98.6 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P774662
CATALOG NUMBER: LD6D95BD010-EU6DR6070959027-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P774662
 CATALOG NUMBER: LD6D95BD010-EU6DR6070959027-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1269435
5°	1300651
10°	1316366
15°	1254016
20°	1105662
25°	894284
30°	604903
35°	303126
40°	49164
45°	48132
50°	49090
55°	49832
60°	51221
65°	52379
70°	53605
75°	54246
80°	52350
85°	43626

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 54246 cd/sqm



TEST NUMBER: P774662

CATALOG NUMBER: LD6D95BD010-EU6DR6070959027-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1133.4	11.6
10°-20°	3066.5	31.3
20°-30°	3299.3	33.7
30°-40°	1434.1	14.7
40°-50°	240.9	2.5
50°-60°	234.2	2.4
60°-70°	200.3	2.0
70°-80°	134.0	1.4
80°-90°	40.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7499.2	76.7
0°-40°	8933.3	91.3
0°-60°	9408.4	96.2
0°-90°	9782.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9782.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11618	
5°	11859	###
15°	11086	3067
25°	7418	3299
35°	2273	1434
45°	312	241
55°	262	234
65°	203	200
75°	128	134
85°	35	40
90°	0	



TEST NUMBER: P774662

CATALOG NUMBER: LD6D95BD010-EU6DR6070959027-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	11618.4
2.5°	11945.0
5°	11858.8
7.5°	11886.1
10°	11864.9
12.5°	11619.9
15°	11086.2
17.5°	10369.5
20°	9509.2
22.5°	8588.3
25°	7418.0
27.5°	5933.2
30°	4794.6
32.5°	3695.4
35°	2272.6
37.5°	972.2
40°	344.7
42.5°	317.5
45°	311.5
47.5°	300.9
50°	288.8
52.5°	275.2
55°	261.6
57.5°	248.0
60°	234.4
62.5°	219.2
65°	202.6
67.5°	186.0
70°	167.8
72.5°	148.2
75°	128.5
77.5°	105.8
80°	83.2
82.5°	59.0
85°	34.8
87.5°	12.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)