

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774740

Luminaire Tested: LD6D95BD010-EU6DR6570959027-6LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P774740  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D95BD010-EU6DR6570959027-6LBSQW1MW  
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8555.1 lumens  
Efficiency: N/A  
Efficacy: 86.2 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 99.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P774740

CATALOG NUMBER: LD6D95BD010-EU6DR6570959027-6LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P774740

CATALOG NUMBER: LD6D95BD010-EU6DR6570959027-6LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	920314
5°	921066
10°	953494
15°	955076
20°	879314
25°	749219
30°	573552
35°	405203
40°	239190
45°	97099
50°	35203
55°	19601
60°	11254
65°	6179
70°	6485
75°	5066
80°	5285
85°	4513

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 97099 cd/sqm



TEST NUMBER: P774740

CATALOG NUMBER: LD6D95BD010-EU6DR6570959027-6LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	811.1	9.5
10°-20°	2339.6	27.3
20°-30°	2807.1	32.8
30°-40°	1886.4	22.1
40°-50°	564.7	6.6
50°-60°	99.6	1.2
60°-70°	28.3	0.3
70°-80°	13.9	0.2
80°-90°	4.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5957.7	69.6
0°-40°	7844.1	91.7
0°-60°	8508.5	99.5
0°-90°	8555.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8555.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8423	
5°	8398	811
15°	8443	2340
25°	6215	2807
35°	3038	1886
45°	628	565
55°	103	100
65°	24	28
75°	12	14
85°	4	4
90°	0	



TEST NUMBER: P774740

CATALOG NUMBER: LD6D95BD010-EU6DR6570959027-6LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	8423.1
2.5°	8459.0
5°	8397.9
7.5°	8524.8
10°	8594.2
12.5°	8577.5
15°	8443.4
17.5°	8115.5
20°	7562.5
22.5°	6911.3
25°	6214.7
27.5°	5428.3
30°	4546.1
32.5°	3746.5
35°	3037.9
37.5°	2337.7
40°	1677.0
42.5°	1095.2
45°	628.4
47.5°	332.8
50°	207.1
52.5°	143.6
55°	102.9
57.5°	74.2
60°	51.5
62.5°	33.5
65°	23.9
67.5°	21.5
70°	20.3
72.5°	15.6
75°	12.0
77.5°	10.8
80°	8.4
82.5°	6.0
85°	3.6
87.5°	2.4
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)