

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774743

Luminaire Tested: LD6D95BD010-EU6DR6570959030-6LBCSSQMW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P774743  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D95BD010-EU6DR6570959030-6LBCSSQMW  
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10022.1 lumens  
Efficiency: N/A  
Efficacy: 101.0 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 99.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P774743

CATALOG NUMBER: LD6D95BD010-EU6DR6570959030-6LBCSSQMW

### Luminous Intensity Polar Plot





TEST NUMBER: P774743

CATALOG NUMBER: LD6D95BD010-EU6DR6570959030-6LBCSSQMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	531458
5°	530117
10°	529663
15°	513341
20°	467334
25°	407251
30°	338719
35°	268387
40°	193705
45°	122374
50°	63784
55°	33907
60°	17801
65°	9798
70°	4115
75°	4536
80°	3162
85°	2680

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 122374 cd/sqm



TEST NUMBER: P774743

CATALOG NUMBER: LD6D95BD010-EU6DR6570959030-6LBCSSQMW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	860.5	8.6
10°-20°	2356.5	23.5
20°-30°	2880.5	28.7
30°-40°	2337.1	23.3
40°-50°	1164.6	11.6
50°-60°	324.9	3.2
60°-70°	73.8	0.7
70°-80°	19.2	0.2
80°-90°	4.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6097.5	60.8
0°-40°	8434.6	84.2
0°-60°	9924.1	99.0
0°-90°	10022.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10022.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9100	
5°	9042	861
15°	8490	2357
25°	6320	2880
35°	3764	2337
45°	1482	1165
55°	333	325
65°	71	74
75°	20	19
85°	4	5
90°	0	



TEST NUMBER: P774743

CATALOG NUMBER: LD6D95BD010-EU6DR6570959030-6LBCSSQMW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	9099.7
2.5°	9093.1
5°	9042.2
7.5°	9012.8
10°	8931.2
12.5°	8765.4
15°	8490.0
17.5°	8059.4
20°	7519.2
22.5°	6936.1
25°	6319.7
27.5°	5660.4
30°	5022.6
32.5°	4392.7
35°	3764.3
37.5°	3137.1
40°	2540.7
42.5°	1981.8
45°	1481.6
47.5°	1032.3
50°	702.0
52.5°	484.1
55°	333.0
57.5°	224.7
60°	152.4
62.5°	105.6
65°	70.9
67.5°	36.1
70°	24.1
72.5°	22.7
75°	20.1
77.5°	13.4
80°	9.4
82.5°	6.7
85°	4.0
87.5°	2.7
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)