

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774688

Luminaire Tested: LD6D95BD010-EU6DR6070959035-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P774688
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR6070959035-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10184.7 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P774688

CATALOG NUMBER: LD6D95BD010-EU6DR6070959035-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P774688

CATALOG NUMBER: LD6D95BD010-EU6DR6070959035-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1321574
5°	1354075
10°	1370431
15°	1305517
20°	1151066
25°	931017
30°	629757
35°	315570
40°	51190
45°	50110
50°	51113
55°	51871
60°	53319
65°	54525
70°	55809
75°	56484
80°	54489
85°	45381

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 56484 cd/sqm



TEST NUMBER: P774688

CATALOG NUMBER: LD6D95BD010-EU6DR6070959035-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1180.0	11.6
10°-20°	3192.4	31.3
20°-30°	3434.8	33.7
30°-40°	1493.1	14.7
40°-50°	250.8	2.5
50°-60°	243.8	2.4
60°-70°	208.5	2.0
70°-80°	139.6	1.4
80°-90°	41.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7807.2	76.7
0°-40°	9300.3	91.3
0°-60°	9794.9	96.2
0°-90°	10184.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10184.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12096	
5°	12346	###
15°	11542	3192
25°	7723	3435
35°	2366	1493
45°	324	251
55°	272	244
65°	211	209
75°	134	140
85°	36	42
90°	0	



TEST NUMBER: P774688

CATALOG NUMBER: LD6D95BD010-EU6DR6070959035-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	12095.6
2.5°	12435.6
5°	12345.9
7.5°	12374.2
10°	12352.2
12.5°	12097.2
15°	11541.5
17.5°	10795.4
20°	9899.7
22.5°	8941.1
25°	7722.7
27.5°	6176.9
30°	4991.6
32.5°	3847.2
35°	2365.9
37.5°	1012.2
40°	358.9
42.5°	330.6
45°	324.3
47.5°	313.3
50°	300.7
52.5°	286.5
55°	272.3
57.5°	258.2
60°	244.0
62.5°	228.2
65°	210.9
67.5°	193.6
70°	174.7
72.5°	154.3
75°	133.8
77.5°	110.2
80°	86.6
82.5°	61.4
85°	36.2
87.5°	12.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)