

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772415

Luminaire Tested: LD6D80BD010-EU6DR6570959035-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P772415
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D80BD010-EU6DR6570959035-6LBCSSQMMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8594.7 lumens
Efficiency: N/A
Efficacy: 108.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P772415
CATALOG NUMBER: LD6D80BD010-EU6DR6570959035-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P772415

CATALOG NUMBER: LD6D80BD010-EU6DR6570959035-6LBCSSQMMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	455772
5°	454623
10°	454234
15°	440233
20°	400775
25°	349247
30°	290480
35°	230164
40°	166121
45°	104946
50°	54707
55°	29071
60°	15267
65°	8402
70°	3518
75°	3881
80°	2691
85°	2278

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 104946 cd/sqm



TEST NUMBER: P772415

CATALOG NUMBER: LD6D80BD010-EU6DR6570959035-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	738.0	8.6
10°-20°	2020.9	23.5
20°-30°	2470.2	28.7
30°-40°	2004.3	23.3
40°-50°	998.8	11.6
50°-60°	278.6	3.2
60°-70°	63.3	0.7
70°-80°	16.5	0.2
80°-90°	4.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5229.1	60.8
0°-40°	7233.4	84.2
0°-60°	8510.7	99.0
0°-90°	8594.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8594.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7804	
5°	7754	738
15°	7281	2021
25°	5420	2470
35°	3228	2004
45°	1271	999
55°	286	279
65°	61	63
75°	17	16
85°	3	4
90°	0	



TEST NUMBER: P772415

CATALOG NUMBER: LD6D80BD010-EU6DR6570959035-6LBCSSQMMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	7803.8
2.5°	7798.0
5°	7754.5
7.5°	7729.2
10°	7659.3
12.5°	7517.1
15°	7280.9
17.5°	6911.6
20°	6448.3
22.5°	5948.3
25°	5419.6
27.5°	4854.3
30°	4307.3
32.5°	3767.1
35°	3228.2
37.5°	2690.3
40°	2178.9
42.5°	1699.5
45°	1270.6
47.5°	885.3
50°	602.1
52.5°	415.1
55°	285.5
57.5°	192.7
60°	130.7
62.5°	90.6
65°	60.8
67.5°	31.0
70°	20.6
72.5°	19.5
75°	17.2
77.5°	11.5
80°	8.0
82.5°	5.7
85°	3.4
87.5°	2.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)