

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772416

Luminaire Tested: LD6D80BD010-EU6DR6570959035-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P772416
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D80BD010-EU6DR6570959035-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8755.1 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P772416

CATALOG NUMBER: LD6D80BD010-EU6DR6570959035-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P772416

CATALOG NUMBER: LD6D80BD010-EU6DR6570959035-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93																			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85																			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78																			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72																			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66																			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61																			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56																			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52																			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49																			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	464276
5°	463106
10°	462708
15°	448444
20°	408252
25°	355769
30°	295902
35°	234456
40°	169217
45°	106903
50°	55725
55°	29621
60°	15559
65°	8554
70°	3586
75°	3949
80°	2758
85°	2345

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 106903 cd/sqm



TEST NUMBER: P772416

CATALOG NUMBER: LD6D80BD010-EU6DR6570959035-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	751.8	8.6
10°-20°	2058.6	23.5
20°-30°	2516.3	28.7
30°-40°	2041.7	23.3
40°-50°	1017.4	11.6
50°-60°	283.8	3.2
60°-70°	64.5	0.7
70°-80°	16.8	0.2
80°-90°	4.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5326.7	60.8
0°-40°	7368.4	84.2
0°-60°	8669.6	99.0
0°-90°	8755.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8755.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7949	
5°	7899	752
15°	7417	2059
25°	5521	2516
35°	3288	2042
45°	1294	1017
55°	291	284
65°	62	64
75°	18	17
85°	4	4
90°	0	



TEST NUMBER: P772416

CATALOG NUMBER: LD6D80BD010-EU6DR6570959035-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7949.4
2.5°	7943.6
5°	7899.2
7.5°	7873.5
10°	7802.2
12.5°	7657.4
15°	7416.7
17.5°	7040.6
20°	6568.6
22.5°	6059.3
25°	5520.8
27.5°	4944.9
30°	4387.7
32.5°	3837.5
35°	3288.4
37.5°	2740.5
40°	2219.5
42.5°	1731.2
45°	1294.3
47.5°	901.8
50°	613.3
52.5°	422.9
55°	290.9
57.5°	196.3
60°	133.2
62.5°	92.3
65°	61.9
67.5°	31.5
70°	21.0
72.5°	19.9
75°	17.5
77.5°	11.7
80°	8.2
82.5°	5.8
85°	3.5
87.5°	2.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)