

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772451

Luminaire Tested: LD6D80BD010-EU6DR6570959050-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P772451
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D80BD010-EU6DR6570959050-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6904.4 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P772451
CATALOG NUMBER: LD6D80BD010-EU6DR6570959050-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P772451

CATALOG NUMBER: LD6D80BD010-EU6DR6570959050-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	742733
5°	743343
10°	769523
15°	770800
20°	709648
25°	604648
30°	462881
35°	327014
40°	193035
45°	78372
50°	28404
55°	15830
60°	9069
65°	4990
70°	5239
75°	4095
80°	4279
85°	3636

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 78372 cd/sqm



TEST NUMBER: P772451

CATALOG NUMBER: LD6D80BD010-EU6DR6570959050-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	654.6	9.5
10°-20°	1888.2	27.3
20°-30°	2265.4	32.8
30°-40°	1522.4	22.0
40°-50°	455.8	6.6
50°-60°	80.4	1.2
60°-70°	22.8	0.3
70°-80°	11.2	0.2
80°-90°	3.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4808.2	69.6
0°-40°	6330.6	91.7
0°-60°	6866.8	99.5
0°-90°	6904.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6904.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6798	
5°	6778	655
15°	6814	1888
25°	5016	2265
35°	2452	1522
45°	507	456
55°	83	80
65°	19	23
75°	10	11
85°	3	4
90°	0	



TEST NUMBER: P772451

CATALOG NUMBER: LD6D80BD010-EU6DR6570959050-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	6797.8
2.5°	6826.8
5°	6777.5
7.5°	6879.9
10°	6936.0
12.5°	6922.5
15°	6814.3
17.5°	6549.6
20°	6103.3
22.5°	5577.8
25°	5015.5
27.5°	4380.9
30°	3668.9
32.5°	3023.6
35°	2451.7
37.5°	1886.6
40°	1353.4
42.5°	883.9
45°	507.2
47.5°	268.6
50°	167.1
52.5°	115.9
55°	83.1
57.5°	59.9
60°	41.5
62.5°	27.0
65°	19.3
67.5°	17.4
70°	16.4
72.5°	12.6
75°	9.7
77.5°	8.7
80°	6.8
82.5°	4.8
85°	2.9
87.5°	1.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)