

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204968

Luminaire Tested: **LD6B10D010 EU6B10209024 6LBCSMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204968
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B10D010 EU6B10209024 6LBCSMMS1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 789.7 lumens
Efficiency: N/A
Efficacy: 79.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204968

CATALOG NUMBER: LD6B10D010 EU6B10209024 6LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P204968

CATALOG NUMBER: LD6B10D010 EU6B10209024 6LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88				88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76				76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65				65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57				57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50				50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44				44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40				40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36				36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32				32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29				29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204968

CATALOG NUMBER: LD6B10D010 EU6B10209024 6LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.2	4.3
10°-20°	95.9	12.1
20°-30°	140.1	17.7
30°-40°	160.2	20.3
40°-50°	153.9	19.5
50°-60°	118.9	15.1
60°-70°	66.4	8.4
70°-80°	19.3	2.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	270.1	34.2
0°-40°	430.3	54.5
0°-60°	703.2	89.0
0°-90°	789.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	789.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	363	
5°	360	34
15°	340	96
25°	304	140
35°	256	160
45°	201	154
55°	133	119
65°	66	66
75°	17	19
85°	0	1
90°	0	



TEST NUMBER: P204968

CATALOG NUMBER: LD6B10D010 EU6B10209024 6LBCSMMS1

CANDELA DISTRIBUTION (FULL):

	0°
0°	362.6
2.5°	362.6
5°	359.6
7.5°	358.0
10°	352.9
12.5°	346.8
15°	340.2
17.5°	333.5
20°	323.8
22.5°	316.2
25°	304.4
27.5°	292.7
30°	280.9
32.5°	269.2
35°	256.4
37.5°	243.6
40°	228.8
42.5°	215.5
45°	200.7
47.5°	183.9
50°	168.0
52.5°	150.7
55°	133.3
57.5°	115.4
60°	98.6
62.5°	81.7
65°	66.4
67.5°	52.1
70°	38.8
72.5°	27.1
75°	16.9
77.5°	8.7
80°	3.1
82.5°	1.0
85°	0.5
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)