

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P35133

Luminaire Tested: **LD6B10D010 EU6B10209027 6LBNB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P35133
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B10D010 EU6B10209027 6LBNB1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 381.8 lumens
Efficiency: N/A
Efficacy: 39.4 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.83
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 9.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P35133

CATALOG NUMBER: LD6B10D010 EU6B10209027 6LBNB1

Luminous Intensity Polar Plot





TEST NUMBER: P35133

CATALOG NUMBER: LD6B10D010 EU6B10209027 6LBNB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88			
3	103	97	92	88	101	96	91	88	93	89	86	91	88	85	88	86	84	82			
4	98	91	86	82	96	90	85	81	88	84	80	86	82	79	84	81	78	77			
5	93	85	80	76	92	85	79	75	83	78	75	81	77	74	80	76	73	72			
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67			
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63			
8	81	72	66	62	80	71	66	62	70	65	61	69	64	61	68	64	61	60			
9	77	68	62	58	76	67	62	58	66	61	58	65	61	58	65	61	58	56			
10	74	64	59	55	73	64	58	55	63	58	55	62	58	55	62	57	54	53			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36665
5°	35037
10°	30540
15°	25531
20°	22009
25°	19652
30°	16875
35°	10991
40°	5195
45°	1476
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P35133

CATALOG NUMBER: LD6B10D010 EU6B10209027 6LBNB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.8	12.8
10°-20°	106.3	27.8
20°-30°	124.9	32.7
30°-40°	86.0	22.5
40°-50°	15.9	4.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	279.9	73.3
0°-40°	365.8	95.8
0°-60°	381.8	100.0
0°-90°	381.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	381.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	562	
5°	535	49
15°	378	106
25°	273	125
35°	138	86
45°	16	16
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P35133

CATALOG NUMBER: LD6B10D010 EU6B10209027 6LBNB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	562
2.5°	557
5°	535
7.5°	504
10°	461
12.5°	418
15°	378
17.5°	344
20°	317
22.5°	294
25°	273
27.5°	252
30°	224
32.5°	184
35°	138
37.5°	96
40°	61
42.5°	34
45°	16
47.5°	5
50°	0
52.5°	0
55°	0
57.5°	0
60°	0
62.5°	0
65°	0
67.5°	0
70°	0
72.5°	0
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)