

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P35131

Luminaire Tested: **LD6B10D010 EU6B10209027 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P35131
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B10D010 EU6B10209027 6LBNWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 587.8 lumens
Efficiency: N/A
Efficacy: 60.6 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 9.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P35131

CATALOG NUMBER: LD6B10D010 EU6B10209027 6LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P35131

CATALOG NUMBER: LD6B10D010 EU6B10209027 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83			
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79			
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74			
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70			
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	67	66			
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63			
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60			
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75288
5°	71253
10°	59424
15°	45658
20°	34158
25°	26634
30°	20717
35°	13062
40°	6473
45°	2399
50°	507
55°	341
60°	261
65°	154
70°	191
75°	0
80°	0
85°	0



TEST NUMBER: P35131

CATALOG NUMBER: LD6B10D010 EU6B10209027 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.7	16.6
10°-20°	187.7	31.9
20°-30°	170.6	29.0
30°-40°	103.4	17.6
40°-50°	23.5	4.0
50°-60°	3.0	0.5
60°-70°	1.4	0.2
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	456.0	77.6
0°-40°	559.5	95.2
0°-60°	586.0	99.7
0°-90°	587.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	587.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1154	
5°	1088	98
15°	676	188
25°	370	171
35°	164	103
45°	26	24
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P35131

CATALOG NUMBER: LD6B10D010 EU6B10209027 6LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1154
2.5°	1140
5°	1088
7.5°	1004
10°	897
12.5°	786
15°	676
17.5°	576
20°	492
22.5°	424
25°	370
27.5°	322
30°	275
32.5°	220
35°	164
37.5°	115
40°	76
42.5°	47
45°	26
47.5°	12
50°	5
52.5°	4
55°	3
57.5°	3
60°	2
62.5°	2
65°	1
67.5°	1
70°	1
72.5°	1
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)