

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773195

Luminaire Tested: LD6D85BD010-EU6DR6570959035-6LBCSSQMMS

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P773195
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR6570959035-6LBCSSQMMMS
Description: 6 INCH SQAURE SHALLOW CAST MATTE METALLIC SILVER TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9149.7 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P773195

CATALOG NUMBER: LD6D85BD010-EU6DR6570959035-6LBCSSQMMS

Luminous Intensity Polar Plot





TEST NUMBER: P773195

CATALOG NUMBER: LD6D85BD010-EU6DR6570959035-6LBCSSQMMMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93				93															
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85															
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78															
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72				72															
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66				66															
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61				61															
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56				56															
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52															
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49				49															
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46				46															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	485202
5°	483977
10°	483566
15°	468658
20°	426656
25°	371802
30°	309235
35°	245023
40°	176848
45°	111727
50°	58232
55°	30955
60°	16260
65°	8941
70°	3757
75°	4129
80°	2859
85°	2479

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 111727 cd/sqm



TEST NUMBER: P773195

CATALOG NUMBER: LD6D85BD010-EU6DR6570959035-6LBCSSQMMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	785.6	8.6
10°-20°	2151.4	23.5
20°-30°	2629.7	28.7
30°-40°	2133.7	23.3
40°-50°	1063.3	11.6
50°-60°	296.6	3.2
60°-70°	67.4	0.7
70°-80°	17.5	0.2
80°-90°	4.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5566.8	60.8
0°-40°	7700.5	84.2
0°-60°	9060.3	99.0
0°-90°	9149.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9149.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8308	
5°	8255	786
15°	7751	2151
25°	5770	2630
35°	3437	2134
45°	1353	1063
55°	304	297
65°	65	67
75°	18	18
85°	4	4
90°	0	



TEST NUMBER: P773195

CATALOG NUMBER: LD6D85BD010-EU6DR6570959035-6LBCSSQMMMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	8307.7
2.5°	8301.6
5°	8255.2
7.5°	8228.3
10°	8153.9
12.5°	8002.5
15°	7751.0
17.5°	7357.9
20°	6864.7
22.5°	6332.4
25°	5769.6
27.5°	5167.7
30°	4585.4
32.5°	4010.4
35°	3436.6
37.5°	2864.0
40°	2319.6
42.5°	1809.3
45°	1352.7
47.5°	942.5
50°	640.9
52.5°	441.9
55°	304.0
57.5°	205.1
60°	139.2
62.5°	96.4
65°	64.7
67.5°	33.0
70°	22.0
72.5°	20.8
75°	18.3
77.5°	12.2
80°	8.5
82.5°	6.1
85°	3.7
87.5°	2.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)