

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204974

Luminaire Tested: **LD6B10D010 EU6B10209727 6LBCSMMS1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204974  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B10D010 EU6B10209727 6LBCSMMS1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 780.7 lumens  
Efficiency: N/A  
Efficacy: 78.9 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204974

CATALOG NUMBER: LD6B10D010 EU6B10209727 6LBCSMMS1

### Luminous Intensity Polar Plot





TEST NUMBER: P204974

CATALOG NUMBER: LD6B10D010 EU6B10209727 6LBCSMMS1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76			
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204974

CATALOG NUMBER: LD6B10D010 EU6B10209727 6LBCSMMS1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	33.8	4.3
10°-20°	94.8	12.1
20°-30°	138.5	17.7
30°-40°	158.4	20.3
40°-50°	152.2	19.5
50°-60°	117.5	15.1
60°-70°	65.6	8.4
70°-80°	19.1	2.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	267.0	34.2
0°-40°	425.4	54.5
0°-60°	695.2	89.0
0°-90°	780.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	780.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	358	
5°	356	34
15°	336	95
25°	301	138
35°	254	158
45°	198	152
55°	132	118
65°	66	66
75°	17	19
85°	0	1
90°	0	



TEST NUMBER: P204974

CATALOG NUMBER: LD6B10D010 EU6B10209727 6LBCSMMS1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	358.5
2.5°	358.5
5°	355.5
7.5°	354.0
10°	348.9
12.5°	342.9
15°	336.3
17.5°	329.7
20°	320.1
22.5°	312.6
25°	300.9
27.5°	289.3
30°	277.7
32.5°	266.1
35°	253.5
37.5°	240.9
40°	226.2
42.5°	213.1
45°	198.4
47.5°	181.8
50°	166.1
52.5°	149.0
55°	131.8
57.5°	114.1
60°	97.5
62.5°	80.8
65°	65.6
67.5°	51.5
70°	38.4
72.5°	26.8
75°	16.7
77.5°	8.6
80°	3.0
82.5°	1.0
85°	0.5
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)