

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203220

Luminaire Tested: **LD6B10D010 EU6B10209727 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203220
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B10D010 EU6B10209727 6LBMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 554.8 lumens
Efficiency: N/A
Efficacy: 56.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203220

CATALOG NUMBER: LD6B10D010 EU6B10209727 6LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P203220

CATALOG NUMBER: LD6B10D010 EU6B10209727 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92				92															
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85															
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78															
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72															
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66				66															
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61				61															
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57				57															
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53				53															
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49				49															
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46				46															

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203220

CATALOG NUMBER: LD6B10D010 EU6B10209727 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.2	9.0
10°-20°	129.9	23.4
20°-30°	168.3	30.3
30°-40°	124.9	22.5
40°-50°	52.7	9.5
50°-60°	18.7	3.4
60°-70°	7.2	1.3
70°-80°	2.5	0.5
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	348.4	62.8
0°-40°	473.3	85.3
0°-60°	544.8	98.2
0°-90°	554.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	554.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	549	
5°	537	50
15°	464	130
25°	373	168
35°	198	125
45°	65	53
55°	20	19
65°	7	7
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P203220

CATALOG NUMBER: LD6B10D010 EU6B10209727 6LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	549.1
2.5°	547.5
5°	537.2
7.5°	522.1
10°	503.9
12.5°	484.1
15°	463.5
17.5°	440.5
20°	419.9
22.5°	398.5
25°	373.2
27.5°	338.3
30°	297.1
32.5°	248.8
35°	198.1
37.5°	155.3
40°	118.1
42.5°	87.9
45°	65.0
47.5°	47.5
50°	34.9
52.5°	26.1
55°	19.8
57.5°	15.1
60°	11.9
62.5°	8.7
65°	7.1
67.5°	5.5
70°	4.0
72.5°	3.2
75°	2.4
77.5°	1.6
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)