

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773218

Luminaire Tested: LD6D85BD010-EU6DR6570959040-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P773218
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR6570959040-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7298.0 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P773218

CATALOG NUMBER: LD6D85BD010-EU6DR6570959040-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P773218

CATALOG NUMBER: LD6D85BD010-EU6DR6570959040-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	785093
5°	785734
10°	813403
15°	814745
20°	750111
25°	639127
30°	489274
35°	345661
40°	204046
45°	82837
50°	30018
55°	16725
60°	9593
65°	5274
70°	5559
75°	4306
80°	4467
85°	3886

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 82837 cd/sqm



TEST NUMBER: P773218

CATALOG NUMBER: LD6D85BD010-EU6DR6570959040-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	691.9	9.5
10°-20°	1995.8	27.3
20°-30°	2394.6	32.8
30°-40°	1609.2	22.1
40°-50°	481.7	6.6
50°-60°	85.0	1.2
60°-70°	24.2	0.3
70°-80°	11.9	0.2
80°-90°	3.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5082.3	69.6
0°-40°	6691.5	91.7
0°-60°	7258.3	99.5
0°-90°	7298.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7298.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7186	
5°	7164	692
15°	7203	1996
25°	5302	2395
35°	2592	1609
45°	536	482
55°	88	85
65°	20	24
75°	10	12
85°	3	4
90°	0	



TEST NUMBER: P773218

CATALOG NUMBER: LD6D85BD010-EU6DR6570959040-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	7185.5
2.5°	7216.1
5°	7164.0
7.5°	7272.3
10°	7331.5
12.5°	7317.2
15°	7202.8
17.5°	6923.0
20°	6451.3
22.5°	5895.8
25°	5301.5
27.5°	4630.7
30°	3878.1
32.5°	3196.0
35°	2591.5
37.5°	1994.2
40°	1430.6
42.5°	934.3
45°	536.1
47.5°	283.9
50°	176.6
52.5°	122.5
55°	87.8
57.5°	63.3
60°	43.9
62.5°	28.6
65°	20.4
67.5°	18.4
70°	17.4
72.5°	13.3
75°	10.2
77.5°	9.2
80°	7.1
82.5°	5.1
85°	3.1
87.5°	2.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)