

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773310

Luminaire Tested: LD6D85BD010-EU6DR7070959050-6LBSQW1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P773310
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR7070959050-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9102.8 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P773310
CATALOG NUMBER: LD6D85BD010-EU6DR7070959050-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P773310
 CATALOG NUMBER: LD6D85BD010-EU6DR7070959050-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1118185
5°	1084958
10°	1054722
15°	1040873
20°	971971
25°	730195
30°	516185
35°	182841
40°	96147
45°	102399
50°	106033
55°	108027
60°	108693
65°	106412
70°	100405
75°	93042
80°	82552
85°	67069

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 108732 cd/sqm



TEST NUMBER: P773310

CATALOG NUMBER: LD6D85BD010-EU6DR7070959050-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	933.0	10.3
10°-20°	2559.3	28.1
20°-30°	2818.7	31.0
30°-40°	1077.0	11.8
40°-50°	508.5	5.6
50°-60°	505.5	5.6
60°-70°	404.8	4.4
70°-80°	232.6	2.6
80°-90°	63.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6311.1	69.3
0°-40°	7388.1	81.2
0°-60°	8402.1	92.3
0°-90°	9102.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9102.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10234	
5°	9892	933
15°	9202	2559
25°	6057	2819
35°	1371	1077
45°	663	508
55°	567	506
65°	412	405
75°	220	233
85°	54	63
90°	0	



TEST NUMBER: P773310

CATALOG NUMBER: LD6D85BD010-EU6DR7070959050-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	10234.1
2.5°	10127.2
5°	9892.2
7.5°	9696.2
10°	9506.6
12.5°	9346.2
15°	9201.9
17.5°	8853.6
20°	8359.4
22.5°	7293.2
25°	6056.9
27.5°	5272.6
30°	4091.4
32.5°	2642.8
35°	1370.8
37.5°	740.5
40°	674.1
42.5°	669.2
45°	662.7
47.5°	648.1
50°	623.8
52.5°	596.3
55°	567.1
57.5°	534.7
60°	497.4
62.5°	455.3
65°	411.6
67.5°	363.0
70°	314.3
72.5°	265.7
75°	220.4
77.5°	173.4
80°	131.2
82.5°	92.4
85°	53.5
87.5°	21.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)