

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203829

Luminaire Tested: **LD6B10D010 EU6B10208030 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203829
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B10D010 EU6B10208030 6LBNGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 534.6 lumens
Efficiency: N/A
Efficacy: 54.0 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203829

CATALOG NUMBER: LD6B10D010 EU6B10208030 6LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P203829

CATALOG NUMBER: LD6B10D010 EU6B10208030 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94																																				
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87																																				
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81																																				
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																																				
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70																																				
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66																																				
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62																																				
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58																																				
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54																																				
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	52	51																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203829

CATALOG NUMBER: LD6B10D010 EU6B10208030 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.8	11.0
10°-20°	145.1	27.1
20°-30°	175.8	32.9
30°-40°	119.8	22.4
40°-50°	28.5	5.3
50°-60°	4.5	0.8
60°-70°	1.6	0.3
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	379.7	71.0
0°-40°	499.5	93.4
0°-60°	532.5	99.6
0°-90°	534.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	534.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	650	
5°	632	59
15°	519	145
25°	384	176
35°	191	120
45°	30	29
55°	5	4
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203829

CATALOG NUMBER: LD6B10D010 EU6B10208030 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	649.9
2.5°	646.2
5°	631.6
7.5°	612.1
10°	584.0
12.5°	552.3
15°	519.4
17.5°	485.3
20°	451.1
22.5°	417.0
25°	384.1
27.5°	353.6
30°	309.7
32.5°	252.4
35°	191.4
37.5°	136.6
40°	90.2
42.5°	56.1
45°	30.5
47.5°	15.9
50°	8.5
52.5°	6.1
55°	4.9
57.5°	3.7
60°	2.4
62.5°	2.4
65°	1.2
67.5°	1.2
70°	1.2
72.5°	1.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)