

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773391

Luminaire Tested: LD6D90BD010-EU6DR3070959024-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P773391
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D90BD010-EU6DR3070959024-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8342.4 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct


Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P773391

CATALOG NUMBER: LD6D90BD010-EU6DR3070959024-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P773391

CATALOG NUMBER: LD6D90BD010-EU6DR3070959024-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89																			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85																			
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82																			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79																			
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																			
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																			
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72																			
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2053254	2053254	2053254
5°	1994311	1991983	1994411
10°	1727382	1715194	1726970
15°	1127026	1120971	1115337
20°	560416	581448	559666
25°	282304	318341	276518
30°	113026	123155	98478
35°	52421	50207	42086
40°	22632	25130	21323
45°	15967	19820	16107
50°	5490	14433	5799
55°	3163	5979	3336
60°	2220	2618	2220
65°	1431	1431	1431
70°	895	582	895
75°	0	384	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 19820 cd/sqm



TEST NUMBER: P773391

CATALOG NUMBER: LD6D90BD010-EU6DR3070959024-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2358.8	28.3
10°-20°	3798.9	45.5
20°-30°	1641.6	19.7
30°-40°	374.2	4.5
40°-50°	128.5	1.5
50°-60°	31.4	0.4
60°-70°	8.1	0.1
70°-80°	0.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7799.4	93.5
0°-40°	8173.5	98.0
0°-60°	8333.4	99.9
0°-90°	8342.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8342.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	26825	26825	26825	26825	26825	
5°	25956	25930	25925	25979	25957	2361
15°	14222	14051	14146	14100	14075	3808
25°	3343	3469	3769	3381	3274	1600
35°	561	573	537	533	450	381
45°	148	183	183	183	149	105
55°	24	25	45	26	25	23
65°	8	8	8	8	8	8
75°	0	0	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P773391

CATALOG NUMBER: LD6D90BD010-EU6DR3070959024-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	26824.7	26824.7	26824.7	26824.7	26824.7
2.5°	26647.0	26628.5	26639.1	26652.2	26657.5
5°	25955.5	25930.5	25925.2	25979.2	25956.8
7.5°	24560.8	24525.3	24471.3	24593.7	24708.3
10°	22224.5	22184.9	22067.7	22125.7	22219.2
12.5°	18775.2	18647.5	18644.8	18829.2	18804.2
15°	14222.3	14051.1	14145.9	14099.9	14074.8
17.5°	9564.1	9498.2	9624.7	9586.5	9421.9
20°	6880.0	6897.2	7138.2	7017.0	6870.8
22.5°	5020.4	5082.3	5368.1	5056.0	4941.4
25°	3342.6	3469.0	3769.3	3380.8	3274.1
27.5°	2055.8	2113.8	2418.0	2029.5	1971.6
30°	1278.8	1249.8	1393.4	1195.8	1114.2
32.5°	838.9	802.1	848.2	761.2	695.4
35°	561.0	572.9	537.3	533.4	450.4
37.5°	350.3	403.0	355.6	379.3	289.7
40°	226.5	292.4	251.5	277.9	213.4
42.5°	185.7	225.2	206.8	219.9	189.6
45°	147.5	183.1	183.1	183.1	148.8
47.5°	81.7	122.5	156.7	125.1	86.9
50°	46.1	61.9	121.2	64.5	48.7
52.5°	31.6	35.6	83.0	36.9	32.9
55°	23.7	25.0	44.8	26.3	25.0
57.5°	18.4	19.8	23.7	19.8	18.4
60°	14.5	14.5	17.1	15.8	14.5
62.5°	10.5	10.5	11.9	10.5	10.5
65°	7.9	7.9	7.9	7.9	7.9
67.5°	4.0	5.3	5.3	5.3	5.3
70°	4.0	2.6	2.6	2.6	4.0
72.5°	2.6	1.3	1.3	1.3	1.3
75°	0.0	0.0	1.3	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)