

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773868

Luminaire Tested: LD6D90BD010-EU6DR6070959024-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P773868
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D90BD010-EU6DR6070959024-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7485.0 lumens
Efficiency: N/A
Efficacy: 75.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 98.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P773868
CATALOG NUMBER: LD6D90BD010-EU6DR6070959024-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P773868

CATALOG NUMBER: LD6D90BD010-EU6DR6070959024-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93															
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86				86															
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80				80															
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75				75															
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70				70															
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66				66															
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62				62															
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59				59															
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55				55															
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53				53															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	971263
5°	995153
10°	1007170
15°	959465
20°	845955
25°	684227
30°	462818
35°	231926
40°	37626
45°	36822
50°	37565
55°	38117
60°	39181
65°	40073
70°	41018
75°	41497
80°	40018
85°	33346

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 41497 cd/sqm



TEST NUMBER: P773868

CATALOG NUMBER: LD6D90BD010-EU6DR6070959024-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	867.2	11.6
10°-20°	2346.2	31.3
20°-30°	2524.3	33.7
30°-40°	1097.3	14.7
40°-50°	184.3	2.5
50°-60°	179.2	2.4
60°-70°	153.2	2.0
70°-80°	102.6	1.4
80°-90°	30.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5737.7	76.7
0°-40°	6835.0	91.3
0°-60°	7198.5	96.2
0°-90°	7485.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7485.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8889	
5°	9073	867
15°	8482	2346
25°	5676	2524
35°	1739	1097
45°	238	184
55°	200	179
65°	155	153
75°	98	103
85°	27	31
90°	0	



TEST NUMBER: P773868

CATALOG NUMBER: LD6D90BD010-EU6DR6070959024-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	8889.4
2.5°	9139.3
5°	9073.4
7.5°	9094.2
10°	9078.0
12.5°	8890.6
15°	8482.2
17.5°	7933.8
20°	7275.6
22.5°	6571.0
25°	5675.6
27.5°	4539.6
30°	3668.4
32.5°	2827.4
35°	1738.8
37.5°	743.9
40°	263.8
42.5°	242.9
45°	238.3
47.5°	230.2
50°	221.0
52.5°	210.6
55°	200.1
57.5°	189.7
60°	179.3
62.5°	167.7
65°	155.0
67.5°	142.3
70°	128.4
72.5°	113.4
75°	98.3
77.5°	81.0
80°	63.6
82.5°	45.1
85°	26.6
87.5°	9.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)