

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204561

Luminaire Tested: **LD6B10D010 EU6B10209730 6LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204561
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B10D010 EU6B10209730 6LB5MW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 861.5 lumens
Efficiency: N/A
Efficacy: 87.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204561

CATALOG NUMBER: LD6B10D010 EU6B10209730 6LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204561

CATALOG NUMBER: LD6B10D010 EU6B10209730 6LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																												
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																												
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																												
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																												
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																												
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																												
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																												
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																												
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																												
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204561

CATALOG NUMBER: LD6B10D010 EU6B10209730 6LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.9	3.8
10°-20°	93.8	10.9
20°-30°	141.2	16.4
30°-40°	168.0	19.5
40°-50°	167.7	19.5
50°-60°	136.4	15.8
60°-70°	83.9	9.7
70°-80°	32.5	3.8
80°-90°	5.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	267.8	31.1
0°-40°	435.8	50.6
0°-60°	739.9	85.9
0°-90°	861.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	861.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	347	
5°	346	33
15°	333	94
25°	307	141
35°	269	168
45°	218	168
55°	153	136
65°	84	84
75°	30	32
85°	4	5
90°	0	



TEST NUMBER: P204561

CATALOG NUMBER: LD6B10D010 EU6B10209730 6LBSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	347.1
2.5°	347.6
5°	346.1
7.5°	344.1
10°	341.5
12.5°	336.9
15°	332.8
17.5°	326.7
20°	320.1
22.5°	313.9
25°	307.3
27.5°	298.1
30°	288.9
32.5°	280.3
35°	269.0
37.5°	256.8
40°	245.5
42.5°	231.8
45°	218.0
47.5°	203.2
50°	187.3
52.5°	171.0
55°	152.6
57.5°	134.8
60°	117.4
62.5°	100.6
65°	84.2
67.5°	68.9
70°	54.6
72.5°	41.3
75°	29.6
77.5°	19.4
80°	11.7
82.5°	7.1
85°	4.1
87.5°	2.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)