

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P252754

Luminaire Tested: **LD6B10D010 EU6B10208035 6LBBA1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P252754
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-2)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B10D010 EU6B10208035 6LBBA1MW
Description: PORTFOLIO 6 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1386.0 lumens
Efficiency: N/A
Efficacy: 137.9 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 10.05
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P252754

CATALOG NUMBER: LD6B10D010 EU6B10208035 6LBBA1MW

Luminous Intensity Polar Plot





TEST NUMBER: P252754

CATALOG NUMBER: LD6B10D010 EU6B10208035 6LBBA1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62			
5	84	73	65	60	82	72	65	60	70	64	59	68	63	58	66	62	58	56			
6	78	67	60	54	77	66	59	54	65	58	54	63	57	53	62	57	53	51			
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	47			
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	53	48	44	43			
9	65	54	46	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62018
5°	61449
10°	60099
15°	58187
20°	55841
25°	52420
30°	45358
35°	35314
40°	26844
45°	20926
50°	17356
55°	15571
60°	14183
65°	13091
70°	12017
75°	11142
80°	10069
85°	9207



TEST NUMBER: P252754

CATALOG NUMBER: LD6B10D010 EU6B10208035 6LBBA1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.6	6.4
10°-20°	242.1	17.5
20°-30°	329.7	23.8
30°-40°	279.0	20.1
40°-50°	178.9	12.9
50°-60°	123.2	8.9
60°-70°	84.1	6.1
70°-80°	46.8	3.4
80°-90°	13.7	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	660.3	47.6
0°-40°	939.3	67.8
0°-60°	1241.4	89.6
0°-90°	1386.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1386.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	951	
5°	938	89
15°	862	242
25°	728	330
35°	443	279
45°	227	179
55°	137	123
65°	85	84
75°	44	47
85°	12	14
90°	0	



TEST NUMBER: P252754

CATALOG NUMBER: LD6B10D010 EU6B10208035 6LBBA1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	950.6
2.5°	947.0
5°	938.3
7.5°	924.5
10°	907.2
12.5°	885.4
15°	861.5
17.5°	834.0
20°	804.3
22.5°	770.9
25°	728.2
27.5°	670.2
30°	602.1
32.5°	523.9
35°	443.4
37.5°	373.2
40°	315.2
42.5°	266.6
45°	226.8
47.5°	195.6
50°	171.0
52.5°	152.2
55°	136.9
57.5°	122.5
60°	108.7
62.5°	96.4
65°	84.8
67.5°	73.2
70°	63.0
72.5°	52.9
75°	44.2
77.5°	35.5
80°	26.8
82.5°	19.6
85°	12.3
87.5°	5.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)