

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204862

Luminaire Tested: **LD6B10D010 EU6B10208035 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204862
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B10D010 EU6B10208035 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1010.9 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204862

CATALOG NUMBER: LD6B10D010 EU6B10208035 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204862

CATALOG NUMBER: LD6B10D010 EU6B10208035 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204862

CATALOG NUMBER: LD6B10D010 EU6B10208035 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.4	4.0
10°-20°	115.0	11.4
20°-30°	172.9	17.1
30°-40°	205.2	20.3
40°-50°	203.0	20.1
50°-60°	159.5	15.8
60°-70°	89.4	8.8
70°-80°	25.1	2.5
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	328.3	32.5
0°-40°	533.5	52.8
0°-60°	896.0	88.6
0°-90°	1010.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1010.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	427	
5°	426	40
15°	408	115
25°	375	173
35°	329	205
45°	264	203
55°	180	159
65°	89	89
75°	22	25
85°	0	0
90°	0	



TEST NUMBER: P204862

CATALOG NUMBER: LD6B10D010 EU6B10208035 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	426.8
2.5°	425.4
5°	426.1
7.5°	422.5
10°	418.2
12.5°	413.1
15°	408.0
17.5°	401.5
20°	392.8
22.5°	384.1
25°	375.4
27.5°	366.0
30°	353.7
32.5°	341.3
35°	329.0
37.5°	314.5
40°	297.9
42.5°	281.9
45°	264.5
47.5°	244.9
50°	224.7
52.5°	201.5
55°	179.7
57.5°	155.1
60°	131.9
62.5°	110.9
65°	89.1
67.5°	70.3
70°	52.2
72.5°	35.5
75°	21.7
77.5°	10.9
80°	2.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)