

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203527

Luminaire Tested: **LD6B10D010 EU6B10209040 6LBMMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203527  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B10D010 EU6B10209040 6LBMMW1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 739.6 lumens  
Efficiency: N/A  
Efficacy: 74.7 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203527

CATALOG NUMBER: LD6B10D010 EU6B10209040 6LBMMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P203527

CATALOG NUMBER: LD6B10D010 EU6B10209040 6LBMMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79		
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71		
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64		
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58		
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53		
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41		
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203527

CATALOG NUMBER: LD6B10D010 EU6B10209040 6LBMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.0	6.9
10°-20°	136.5	18.5
20°-30°	183.3	24.8
30°-40°	150.4	20.3
40°-50°	90.3	12.2
50°-60°	60.0	8.1
60°-70°	40.2	5.4
70°-80°	21.6	2.9
80°-90°	6.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	370.9	50.1
0°-40°	521.2	70.5
0°-60°	671.6	90.8
0°-90°	739.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	739.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	552	
5°	543	51
15°	487	137
25°	404	183
35°	239	150
45°	114	90
55°	66	60
65°	41	40
75°	20	22
85°	5	6
90°	0	



TEST NUMBER: P203527

CATALOG NUMBER: LD6B10D010 EU6B10209040 6LBMMW1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	551.8
2.5°	547.8
5°	542.7
7.5°	531.4
10°	518.2
12.5°	501.9
15°	486.6
17.5°	468.2
20°	449.8
22.5°	429.4
25°	403.9
27.5°	373.3
30°	332.5
32.5°	286.6
35°	238.7
37.5°	197.9
40°	163.2
42.5°	135.7
45°	114.2
47.5°	96.9
50°	84.7
52.5°	74.5
55°	66.3
57.5°	59.2
60°	53.0
62.5°	45.9
65°	40.8
67.5°	34.7
70°	29.6
72.5°	24.5
75°	20.4
77.5°	16.3
80°	12.2
82.5°	9.2
85°	5.1
87.5°	2.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)