

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204454

Luminaire Tested: **LD6B10D010 EU6B10209040 6LBSB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204454  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B10D010 EU6B10209040 6LBSB1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 844.2 lumens  
Efficiency: N/A  
Efficacy: 85.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204454

CATALOG NUMBER: LD6B10D010 EU6B10209040 6LBSB1

### Luminous Intensity Polar Plot





TEST NUMBER: P204454

CATALOG NUMBER: LD6B10D010 EU6B10209040 6LBSB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88																			
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76																			
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65																			
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44																			
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39																			
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35																			
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32																			
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204454

CATALOG NUMBER: LD6B10D010 EU6B10209040 6LBSB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	35.1	4.2
10°-20°	99.7	11.8
20°-30°	148.4	17.6
30°-40°	172.6	20.4
40°-50°	168.3	19.9
50°-60°	129.4	15.3
60°-70°	71.5	8.5
70°-80°	19.0	2.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	283.2	33.5
0°-40°	455.9	54.0
0°-60°	753.5	89.3
0°-90°	844.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	844.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	372	
5°	370	35
15°	353	100
25°	322	148
35°	277	173
45°	218	168
55°	144	129
65°	72	72
75°	16	19
85°	0	0
90°	0	



TEST NUMBER: P204454

CATALOG NUMBER: LD6B10D010 EU6B10209040 6LBSB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	372.4
2.5°	372.4
5°	370.2
7.5°	367.0
10°	364.9
12.5°	358.5
15°	353.1
17.5°	347.8
20°	340.3
22.5°	332.8
25°	322.1
27.5°	311.4
30°	300.7
32.5°	288.9
35°	277.2
37.5°	262.2
40°	249.3
42.5°	235.4
45°	218.3
47.5°	202.2
50°	184.1
52.5°	164.8
55°	144.5
57.5°	125.2
60°	107.0
62.5°	88.8
65°	71.7
67.5°	55.6
70°	40.7
72.5°	27.8
75°	16.1
77.5°	7.5
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)