

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P252762

Luminaire Tested: **LD6B10D010 EU6B10209050 6LBBA1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P252762
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1712-453-2)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B10D010 EU6B10209050 6LBBA1MW
Description: PORTFOLIO 6 INCH BAFFLE RECESSED DOWNLIGHT, WITH MATTE WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1178.1 lumens
Efficiency: N/A
Efficacy: 117.2 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 10.05
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P252762

CATALOG NUMBER: LD6B10D010 EU6B10209050 6LBBA1MW

Luminous Intensity Polar Plot





TEST NUMBER: P252762

CATALOG NUMBER: LD6B10D010 EU6B10209050 6LBBA1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88			
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			
4	90	80	72	67	87	78	72	66	76	70	66	74	69	65	72	68	64	62			
5	84	73	65	60	82	72	65	60	70	64	59	68	63	58	66	62	58	56			
6	78	67	60	54	77	66	59	54	65	58	54	63	57	53	62	57	53	51			
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	47			
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	53	48	44	43			
9	65	54	46	42	64	53	46	42	52	46	41	51	45	41	50	45	41	39			
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52714
5°	52228
10°	51076
15°	49454
20°	47461
25°	44552
30°	38556
35°	30018
40°	22816
45°	17789
50°	14747
55°	13240
60°	12056
65°	11130
70°	10224
75°	9478
80°	8566
85°	7860



TEST NUMBER: P252762

CATALOG NUMBER: LD6B10D010 EU6B10209050 6LBBA1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.3	6.4
10°-20°	205.7	17.5
20°-30°	280.2	23.8
30°-40°	237.1	20.1
40°-50°	152.1	12.9
50°-60°	104.7	8.9
60°-70°	71.5	6.1
70°-80°	39.8	3.4
80°-90°	11.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	561.2	47.6
0°-40°	798.3	67.8
0°-60°	1055.1	89.6
0°-90°	1178.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1178.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	808	
5°	798	75
15°	732	206
25°	619	280
35°	377	237
45°	193	152
55°	116	105
65°	72	72
75°	38	40
85°	10	12
90°	0	



TEST NUMBER: P252762

CATALOG NUMBER: LD6B10D010 EU6B10209050 6LBBA1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	808.0
2.5°	804.9
5°	797.5
7.5°	785.8
10°	771.0
12.5°	752.5
15°	732.2
17.5°	708.8
20°	683.6
22.5°	655.2
25°	618.9
27.5°	569.6
30°	511.8
32.5°	445.2
35°	376.9
37.5°	317.2
40°	267.9
42.5°	226.6
45°	192.8
47.5°	166.3
50°	145.3
52.5°	129.3
55°	116.4
57.5°	104.1
60°	92.4
62.5°	81.9
65°	72.1
67.5°	62.2
70°	53.6
72.5°	45.0
75°	37.6
77.5°	30.2
80°	22.8
82.5°	16.6
85°	10.5
87.5°	4.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)