

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203219

Luminaire Tested: **LD6B10D010 EU6B10209050 6LBMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203219  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B10D010 EU6B10209050 6LBMH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 677.0 lumens  
Efficiency: N/A  
Efficacy: 68.4 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203219

CATALOG NUMBER: LD6B10D010 EU6B10209050 6LBMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203219

CATALOG NUMBER: LD6B10D010 EU6B10209050 6LBMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53			
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49			
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203219

CATALOG NUMBER: LD6B10D010 EU6B10209050 6LBMH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	61.3	9.0
10°-20°	158.5	23.4
20°-30°	205.3	30.3
30°-40°	152.4	22.5
40°-50°	64.3	9.5
50°-60°	22.9	3.4
60°-70°	8.8	1.3
70°-80°	3.1	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	425.1	62.8
0°-40°	577.5	85.3
0°-60°	664.7	98.2
0°-90°	677.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	677.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	670	
5°	655	61
15°	566	158
25°	455	205
35°	242	152
45°	79	64
55°	24	23
65°	9	9
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P203219

CATALOG NUMBER: LD6B10D010 EU6B10209050 6LBMH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	669.9
2.5°	668.0
5°	655.4
7.5°	637.1
10°	614.8
12.5°	590.7
15°	565.5
17.5°	537.5
20°	512.4
22.5°	486.3
25°	455.3
27.5°	412.8
30°	362.5
32.5°	303.6
35°	241.7
37.5°	189.5
40°	144.0
42.5°	107.3
45°	79.3
47.5°	58.0
50°	42.5
52.5°	31.9
55°	24.2
57.5°	18.4
60°	14.5
62.5°	10.6
65°	8.7
67.5°	6.8
70°	4.8
72.5°	3.9
75°	2.9
77.5°	1.9
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)