

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204455

Luminaire Tested: **LD6B10D010 EU6B10209050 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204455
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B10D010 EU6B10209050 6LBSB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 847.7 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204455

CATALOG NUMBER: LD6B10D010 EU6B10209050 6LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P204455

CATALOG NUMBER: LD6B10D010 EU6B10209050 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76			76
3	94	84	77	72	91	83	76	71	80	74	70	77	73	69	75	71	67	65			65
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50			50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44			44
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39			39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35			35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32			32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29			29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204455

CATALOG NUMBER: LD6B10D010 EU6B10209050 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.3	4.2
10°-20°	100.2	11.8
20°-30°	149.0	17.6
30°-40°	173.4	20.5
40°-50°	169.0	19.9
50°-60°	130.0	15.3
60°-70°	71.9	8.5
70°-80°	19.0	2.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	284.4	33.6
0°-40°	457.8	54.0
0°-60°	756.7	89.3
0°-90°	847.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	847.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	374	
5°	372	35
15°	355	100
25°	324	149
35°	278	173
45°	219	169
55°	145	130
65°	72	72
75°	16	19
85°	0	0
90°	0	



TEST NUMBER: P204455

CATALOG NUMBER: LD6B10D010 EU6B10209050 6LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	374.0
2.5°	374.0
5°	371.8
7.5°	368.6
10°	366.5
12.5°	360.0
15°	354.6
17.5°	349.3
20°	341.8
22.5°	334.2
25°	323.5
27.5°	312.7
30°	302.0
32.5°	290.2
35°	278.3
37.5°	263.3
40°	250.4
42.5°	236.4
45°	219.2
47.5°	203.1
50°	184.8
52.5°	165.5
55°	145.1
57.5°	125.7
60°	107.5
62.5°	89.2
65°	72.0
67.5°	55.9
70°	40.8
72.5°	27.9
75°	16.1
77.5°	7.5
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)