

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203531

Luminaire Tested: **LD6B15D010 EU6B10208027 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203531
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B15D010 EU6B10208027 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1125.1 lumens
Efficiency: N/A
Efficacy: 78.7 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203531

CATALOG NUMBER: LD6B15D010 EU6B10208027 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203531

CATALOG NUMBER: LD6B15D010 EU6B10208027 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79		
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71		
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64		
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58		
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53		
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41		
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203531

CATALOG NUMBER: LD6B15D010 EU6B10208027 6LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.5	6.9
10°-20°	207.7	18.5
20°-30°	278.9	24.8
30°-40°	228.8	20.3
40°-50°	137.4	12.2
50°-60°	91.3	8.1
60°-70°	61.2	5.4
70°-80°	32.9	2.9
80°-90°	9.3	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	564.2	50.1
0°-40°	793.0	70.5
0°-60°	1021.7	90.8
0°-90°	1125.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1125.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	840	
5°	826	78
15°	740	208
25°	614	279
35°	363	229
45°	174	137
55°	101	91
65°	62	61
75°	31	33
85°	8	9
90°	0	



TEST NUMBER: P203531

CATALOG NUMBER: LD6B15D010 EU6B10208027 6LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	839.5
2.5°	833.3
5°	825.5
7.5°	808.5
10°	788.3
12.5°	763.5
15°	740.2
17.5°	712.2
20°	684.3
22.5°	653.3
25°	614.5
27.5°	567.9
30°	505.9
32.5°	436.0
35°	363.1
37.5°	301.0
40°	248.3
42.5°	206.4
45°	173.8
47.5°	147.4
50°	128.8
52.5°	113.3
55°	100.9
57.5°	90.0
60°	80.7
62.5°	69.8
65°	62.1
67.5°	52.8
70°	45.0
72.5°	37.2
75°	31.0
77.5°	24.8
80°	18.6
82.5°	14.0
85°	7.8
87.5°	3.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)