

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205391

Luminaire Tested: **LD6B15D010 EU6B10209727 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205391
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B15D010 EU6B10209727 6LBSLI1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1128.7 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205391

CATALOG NUMBER: LD6B15D010 EU6B10209727 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205391

CATALOG NUMBER: LD6B15D010 EU6B10209727 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77																			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68																			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60																			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53																			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47																			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43																			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39																			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36																			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205391

CATALOG NUMBER: LD6B15D010 EU6B10209727 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.6	5.8
10°-20°	167.1	14.8
20°-30°	213.1	18.9
30°-40°	221.0	19.6
40°-50°	203.6	18.0
50°-60°	153.2	13.6
60°-70°	82.7	7.3
70°-80°	22.2	2.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	445.8	39.5
0°-40°	666.8	59.1
0°-60°	1023.5	90.7
0°-90°	1128.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1128.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	712	
5°	702	66
15°	596	167
25°	463	213
35°	352	221
45°	265	204
55°	172	153
65°	83	83
75°	19	22
85°	0	0
90°	0	



TEST NUMBER: P205391

CATALOG NUMBER: LD6B15D010 EU6B10209727 6LBSL11

CANDELA DISTRIBUTION (FULL):

	0°
0°	712.3
2.5°	709.9
5°	701.5
7.5°	685.9
10°	658.3
12.5°	630.7
15°	596.0
17.5°	563.6
20°	530.0
22.5°	495.2
25°	462.9
27.5°	431.7
30°	402.9
32.5°	376.5
35°	352.5
37.5°	329.8
40°	308.2
42.5°	285.4
45°	265.0
47.5°	242.2
50°	219.4
52.5°	195.5
55°	171.5
57.5°	147.5
60°	124.7
62.5°	103.1
65°	82.7
67.5°	63.6
70°	46.8
72.5°	32.4
75°	19.2
77.5°	8.4
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)