

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774572

Luminaire Tested: LD6D95BD010-EU6DR5570959027-6LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774572
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR5570959027-6LBCSSQMB
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10907.1 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P774572

CATALOG NUMBER: LD6D95BD010-EU6DR5570959027-6LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P774572

CATALOG NUMBER: LD6D95BD010-EU6DR5570959027-6LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94								
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87								
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81								
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75								
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70								
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65								
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61								
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57								
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54								
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50								

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1336325
5°	1283256
10°	1278423
15°	1241698
20°	1113359
25°	920131
30°	695047
35°	503960
40°	322514
45°	147302
50°	48172
55°	20782
60°	8938
65°	1163
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 147302 cd/sqm



TEST NUMBER: P774572

CATALOG NUMBER: LD6D95BD010-EU6DR5570959027-6LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1113.3	10.2
10°-20°	3038.5	27.9
20°-30°	3462.7	31.7
30°-40°	2357.2	21.6
40°-50°	812.3	7.4
50°-60°	112.3	1.0
60°-70°	10.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7614.5	69.8
0°-40°	9971.7	91.4
0°-60°	10896.3	99.9
0°-90°	10907.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10907.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12231	
5°	11700	###
15°	10977	3039
25°	7632	3463
35°	3778	2357
45°	953	812
55°	109	112
65°	4	11
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774572

CATALOG NUMBER: LD6D95BD010-EU6DR5570959027-6LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	12230.6
2.5°	11950.2
5°	11700.2
7.5°	11577.4
10°	11522.9
12.5°	11341.0
15°	10977.3
17.5°	10399.8
20°	9575.4
22.5°	8623.6
25°	7632.4
27.5°	6600.3
30°	5509.1
32.5°	4584.6
35°	3778.3
37.5°	3011.4
40°	2261.2
42.5°	1567.1
45°	953.3
47.5°	513.8
50°	283.4
52.5°	168.2
55°	109.1
57.5°	69.7
60°	40.9
62.5°	18.2
65°	4.5
67.5°	1.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)