

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774652

Luminaire Tested: LD6D95BD010-EU6DR6070959027-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774652
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR6070959027-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10677.1 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P774652
CATALOG NUMBER: LD6D95BD010-EU6DR6070959027-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P774652

CATALOG NUMBER: LD6D95BD010-EU6DR6070959027-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 | 101 | 99 | 98 | 97 | 96 | 95 | 94 | | | | | | | | | | | | | | | | | | | |
| 2 | 108 | 103 | 99 | 96 | 106 | 101 | 98 | 95 | 98 | 95 | 92 | 95 | 93 | 90 | 92 | 90 | 89 | 87 | | | | | | | | | | | | | | | | | | | |
| 3 | 102 | 96 | 91 | 87 | 100 | 95 | 90 | 86 | 92 | 88 | 85 | 90 | 86 | 84 | 87 | 85 | 82 | 81 | | | | | | | | | | | | | | | | | | | |
| 4 | 97 | 90 | 84 | 80 | 95 | 88 | 83 | 79 | 86 | 82 | 78 | 84 | 81 | 78 | 82 | 79 | 77 | 75 | | | | | | | | | | | | | | | | | | | |
| 5 | 92 | 84 | 78 | 74 | 91 | 83 | 77 | 73 | 81 | 76 | 73 | 79 | 75 | 72 | 78 | 74 | 71 | 70 | | | | | | | | | | | | | | | | | | | |
| 6 | 87 | 79 | 73 | 68 | 86 | 78 | 72 | 68 | 76 | 71 | 68 | 75 | 70 | 67 | 74 | 70 | 67 | 65 | | | | | | | | | | | | | | | | | | | |
| 7 | 83 | 74 | 68 | 63 | 82 | 73 | 67 | 63 | 72 | 67 | 63 | 71 | 66 | 63 | 69 | 65 | 62 | 61 | | | | | | | | | | | | | | | | | | | |
| 8 | 79 | 69 | 63 | 59 | 78 | 69 | 63 | 59 | 68 | 63 | 59 | 67 | 62 | 59 | 66 | 61 | 58 | 57 | | | | | | | | | | | | | | | | | | | |
| 9 | 75 | 65 | 59 | 55 | 74 | 65 | 59 | 55 | 64 | 59 | 55 | 63 | 58 | 55 | 62 | 58 | 55 | 53 | | | | | | | | | | | | | | | | | | | |
| 10 | 72 | 62 | 56 | 52 | 71 | 61 | 56 | 52 | 61 | 55 | 52 | 60 | 55 | 52 | 59 | 55 | 52 | 50 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 1167451 |
| 5° | 1164595 |
| 10° | 1203279 |
| 15° | 1204517 |
| 20° | 1108290 |
| 25° | 942675 |
| 30° | 718286 |
| 35° | 507948 |
| 40° | 298267 |
| 45° | 120354 |
| 50° | 40183 |
| 55° | 19335 |
| 60° | 7954 |
| 65° | 1163 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 120354 cd/sqm



TEST NUMBER: P774652

CATALOG NUMBER: LD6D95BD010-EU6DR6070959027-6LBCSSQMW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 1024.3 | 9.6 |
| 10°-20° | 2950.0 | 27.6 |
| 20°-30° | 3530.8 | 33.1 |
| 30°-40° | 2361.6 | 22.1 |
| 40°-50° | 700.2 | 6.6 |
| 50°-60° | 100.7 | 0.9 |
| 60°-70° | 9.6 | 0.1 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 7505.1 | 70.3 |
| 0°-40° | 9866.7 | 92.4 |
| 0°-60° | 10667.5 | 99.9 |
| 0°-90° | 10677.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 10677.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 10685 | |
| 5° | 10618 | ### |
| 15° | 10649 | 2950 |
| 25° | 7819 | 3531 |
| 35° | 3808 | 2362 |
| 45° | 779 | 700 |
| 55° | 102 | 101 |
| 65° | 4 | 10 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P774652

CATALOG NUMBER: LD6D95BD010-EU6DR6070959027-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|---------|
| 0° | 10685.0 |
| 2.5° | 10671.3 |
| 5° | 10618.3 |
| 7.5° | 10762.3 |
| 10° | 10845.6 |
| 12.5° | 10830.4 |
| 15° | 10648.6 |
| 17.5° | 10219.7 |
| 20° | 9531.8 |
| 22.5° | 8705.9 |
| 25° | 7819.4 |
| 27.5° | 6820.7 |
| 30° | 5693.3 |
| 32.5° | 4687.1 |
| 35° | 3808.2 |
| 37.5° | 2927.7 |
| 40° | 2091.2 |
| 42.5° | 1379.0 |
| 45° | 778.9 |
| 47.5° | 398.5 |
| 50° | 236.4 |
| 52.5° | 153.1 |
| 55° | 101.5 |
| 57.5° | 65.2 |
| 60° | 36.4 |
| 62.5° | 15.2 |
| 65° | 4.5 |
| 67.5° | 1.5 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)