

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774730

Luminaire Tested: LD6D95BD010-EU6DR6570959027-6LBCSSQMW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P774730  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D95BD010-EU6DR6570959027-6LBCSSQMW  
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9728.1 lumens  
Efficiency: N/A  
Efficacy: 98.1 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96  
Luminous Opening: Circular (Dia: 0.48' x H: 0')  
CIE Type: Direct


Input Watts (W): 99.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P774730

CATALOG NUMBER: LD6D95BD010-EU6DR6570959027-6LBCSSQMW

### Luminous Intensity Polar Plot





TEST NUMBER: P774730

CATALOG NUMBER: LD6D95BD010-EU6DR6570959027-6LBCSSQMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93			
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72			
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66			
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61			
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	515870
5°	514569
10°	514131
15°	498279
20°	453623
25°	395304
30°	328779
35°	260508
40°	188025
45°	118789
50°	61912
55°	32910
60°	17288
65°	9508
70°	3996
75°	4400
80°	3061
85°	2613

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 118789 cd/sqm



TEST NUMBER: P774730

CATALOG NUMBER: LD6D95BD010-EU6DR6570959027-6LBCSSQMW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	835.3	8.6
10°-20°	2287.4	23.5
20°-30°	2796.0	28.7
30°-40°	2268.6	23.3
40°-50°	1130.5	11.6
50°-60°	315.3	3.2
60°-70°	71.6	0.7
70°-80°	18.7	0.2
80°-90°	4.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5918.6	60.8
0°-40°	8187.2	84.2
0°-60°	9633.0	99.0
0°-90°	9728.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9728.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8833	
5°	8777	835
15°	8241	2287
25°	6134	2796
35°	3654	2269
45°	1438	1130
55°	323	315
65°	69	72
75°	20	19
85°	4	5
90°	0	



TEST NUMBER: P774730

CATALOG NUMBER: LD6D95BD010-EU6DR6570959027-6LBCSSQMW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	8832.8
2.5°	8826.3
5°	8777.0
7.5°	8748.4
10°	8669.3
12.5°	8508.3
15°	8240.9
17.5°	7823.0
20°	7298.6
22.5°	6732.7
25°	6134.3
27.5°	5494.4
30°	4875.2
32.5°	4263.9
35°	3653.8
37.5°	3045.1
40°	2466.2
42.5°	1923.6
45°	1438.2
47.5°	1002.0
50°	681.4
52.5°	469.9
55°	323.2
57.5°	218.1
60°	148.0
62.5°	102.5
65°	68.8
67.5°	35.0
70°	23.4
72.5°	22.1
75°	19.5
77.5°	13.0
80°	9.1
82.5°	6.5
85°	3.9
87.5°	2.6
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)