

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774739

Luminaire Tested: LD6D95BD010-EU6DR6570959027-6LBSQW1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P774739
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR6570959027-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7277.0 lumens
Efficiency: N/A
Efficacy: 73.4 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P774739
CATALOG NUMBER: LD6D95BD010-EU6DR6570959027-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P774739

CATALOG NUMBER: LD6D95BD010-EU6DR6570959027-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	782821
5°	783464
10°	811051
15°	812392
20°	747948
25°	637283
30°	487861
35°	344674
40°	203447
45°	82590
50°	29933
55°	16687
60°	9571
65°	5274
70°	5527
75°	4306
80°	4467
85°	3886

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 82590 cd/sqm



TEST NUMBER: P774739

CATALOG NUMBER: LD6D95BD010-EU6DR6570959027-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	689.9	9.5
10°-20°	1990.1	27.3
20°-30°	2387.7	32.8
30°-40°	1604.6	22.1
40°-50°	480.3	6.6
50°-60°	84.8	1.2
60°-70°	24.1	0.3
70°-80°	11.8	0.2
80°-90°	3.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5067.6	69.6
0°-40°	6672.2	91.7
0°-60°	7237.3	99.5
0°-90°	7277.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7277.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7165	
5°	7143	690
15°	7182	1990
25°	5286	2388
35°	2584	1605
45°	534	480
55°	88	85
65°	20	24
75°	10	12
85°	3	4
90°	0	



TEST NUMBER: P774739

CATALOG NUMBER: LD6D95BD010-EU6DR6570959027-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	7164.7
2.5°	7195.3
5°	7143.3
7.5°	7251.3
10°	7310.3
12.5°	7296.1
15°	7182.0
17.5°	6903.1
20°	6432.7
22.5°	5878.8
25°	5286.2
27.5°	4617.3
30°	3866.9
32.5°	3186.8
35°	2584.1
37.5°	1988.4
40°	1426.4
42.5°	931.6
45°	534.5
47.5°	283.0
50°	176.1
52.5°	122.2
55°	87.6
57.5°	63.1
60°	43.8
62.5°	28.5
65°	20.4
67.5°	18.3
70°	17.3
72.5°	13.2
75°	10.2
77.5°	9.2
80°	7.1
82.5°	5.1
85°	3.1
87.5°	2.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)