

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204460

Luminaire Tested: **LD6B15D010 EU6B10208035 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204460
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B15D010 EU6B10208035 6LBSB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1375.7 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204460

CATALOG NUMBER: LD6B15D010 EU6B10208035 6LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P204460

CATALOG NUMBER: LD6B15D010 EU6B10208035 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88				88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76				76
3	94	84	77	72	91	83	76	71	80	74	70	77	73	69	75	71	67	65				65
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57				57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50				50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44				44
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39				39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35				35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32				32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29				29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204460

CATALOG NUMBER: LD6B15D010 EU6B10208035 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.3	4.2
10°-20°	162.5	11.8
20°-30°	241.8	17.6
30°-40°	281.3	20.5
40°-50°	274.2	19.9
50°-60°	210.9	15.3
60°-70°	116.6	8.5
70°-80°	30.9	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	461.6	33.6
0°-40°	742.9	54.0
0°-60°	1228.0	89.3
0°-90°	1375.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1375.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	607	
5°	603	57
15°	576	163
25°	525	242
35°	452	281
45°	356	274
55°	235	211
65°	117	117
75°	26	31
85°	0	0
90°	0	



TEST NUMBER: P204460

CATALOG NUMBER: LD6B15D010 EU6B10208035 6LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	606.9
2.5°	606.9
5°	603.4
7.5°	598.2
10°	594.7
12.5°	584.2
15°	575.5
17.5°	566.8
20°	554.6
22.5°	542.4
25°	524.9
27.5°	507.5
30°	490.0
32.5°	470.9
35°	451.7
37.5°	427.3
40°	406.3
42.5°	383.7
45°	355.8
47.5°	329.6
50°	299.9
52.5°	268.6
55°	235.4
57.5°	204.0
60°	174.4
62.5°	144.7
65°	116.8
67.5°	90.7
70°	66.3
72.5°	45.3
75°	26.2
77.5°	12.2
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)