

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774284

Luminaire Tested: LD6D95BD010-EU6DR3570959030-6LBSQW1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774284
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR3570959030-6LBSQW1B
Description: 6 INCH SQAURE DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9151.0 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P774284
CATALOG NUMBER: LD6D95BD010-EU6DR3570959030-6LBSQW1B

Luminous Intensity Polar Plot





TEST NUMBER: P774284

CATALOG NUMBER: LD6D95BD010-EU6DR3570959030-6LBSQW1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96																												
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92																												
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88																												
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84																												
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81																												
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78																												
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75																												
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72																												
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70																												
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2751077
5°	2686434
10°	2421192
15°	1879226
20°	1065873
25°	414676
30°	154702
35°	84805
40°	55426
45°	33731
50°	21468
55°	15163
60°	11101
65°	6024
70°	447
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 33731 cd/sqm



TEST NUMBER: P774284

CATALOG NUMBER: LD6D95BD010-EU6DR3570959030-6LBSQW1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2252.7	24.6
10°-20°	4398.3	48.1
20°-30°	1793.8	19.6
30°-40°	429.3	4.7
40°-50°	178.9	2.0
50°-60°	74.0	0.8
60°-70°	23.2	0.3
70°-80°	0.5	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8444.7	92.3
0°-40°	8874.0	97.0
0°-60°	9126.9	99.7
0°-90°	9151.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9151.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	25179	
5°	24494	###
15°	16613	4398
25°	3440	1794
35°	636	429
45°	218	179
55°	80	74
65°	23	23
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P774284

CATALOG NUMBER: LD6D95BD010-EU6DR3570959030-6LBSQW1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	25179.0
2.5°	25027.9
5°	24493.8
7.5°	23428.3
10°	21823.1
12.5°	19562.9
15°	16613.4
17.5°	13006.2
20°	9167.0
22.5°	5845.4
25°	3439.7
27.5°	1944.3
30°	1226.2
32.5°	860.9
35°	635.8
37.5°	491.6
40°	388.6
42.5°	299.3
45°	218.3
47.5°	163.4
50°	126.3
52.5°	100.2
55°	79.6
57.5°	64.5
60°	50.8
62.5°	37.1
65°	23.3
67.5°	8.2
70°	1.4
72.5°	1.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)