

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204260

Luminaire Tested: **LD6B15D010 EU6B10209035 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204260
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B15D010 EU6B10209035 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1330.0 lumens
Efficiency: N/A
Efficacy: 93.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204260

CATALOG NUMBER: LD6B15D010 EU6B10209035 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204260

CATALOG NUMBER: LD6B15D010 EU6B10209035 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89				89
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77				77
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67				67
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59				59
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52				52
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47				47
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42				42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38				38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35				35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204260

CATALOG NUMBER: LD6B15D010 EU6B10209035 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.2	5.5
10°-20°	189.4	14.2
20°-30°	247.7	18.6
30°-40°	262.3	19.7
40°-50°	244.6	18.4
50°-60°	185.3	13.9
60°-70°	100.3	7.5
70°-80°	26.9	2.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	510.2	38.4
0°-40°	772.5	58.1
0°-60°	1202.4	90.4
0°-90°	1330.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1330.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	793	
5°	782	73
15°	677	189
25°	538	248
35°	419	262
45°	319	245
55°	208	185
65°	100	100
75°	23	27
85°	0	0
90°	0	



TEST NUMBER: P204260

CATALOG NUMBER: LD6B15D010 EU6B10209035 6LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	793.2
2.5°	790.3
5°	781.6
7.5°	762.6
10°	737.9
12.5°	708.8
15°	676.8
17.5°	640.4
20°	608.4
22.5°	572.0
25°	538.5
27.5°	505.0
30°	473.0
32.5°	445.4
35°	419.2
37.5°	393.0
40°	368.2
42.5°	343.5
45°	318.7
47.5°	291.1
50°	263.4
52.5°	235.8
55°	208.1
57.5°	179.0
60°	151.4
62.5°	125.2
65°	100.4
67.5°	77.1
70°	56.8
72.5°	39.3
75°	23.3
77.5°	10.2
80°	2.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)