

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774766

Luminaire Tested: LD6D95BD010-EU6DR6570959035-6LBSQW1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P774766  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD6D95BD010-EU6DR6570959035-6LBSQW1MW  
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8906.4 lumens  
Efficiency: N/A  
Efficacy: 89.8 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 99.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P774766

CATALOG NUMBER: LD6D95BD010-EU6DR6570959035-6LBSQW1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P774766

CATALOG NUMBER: LD6D95BD010-EU6DR6570959035-6LBSQW1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	958108
5°	958905
10°	992659
15°	994304
20°	915428
25°	779985
30°	597106
35°	421850
40°	249003
45°	101086
50°	36648
55°	20421
60°	11713
65°	6437
70°	6772
75°	5277
80°	5474
85°	4638

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 101086 cd/sqm



TEST NUMBER: P774766

CATALOG NUMBER: LD6D95BD010-EU6DR6570959035-6LBSQW1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	844.4	9.5
10°-20°	2435.7	27.3
20°-30°	2922.3	32.8
30°-40°	1963.9	22.1
40°-50°	587.9	6.6
50°-60°	103.8	1.2
60°-70°	29.5	0.3
70°-80°	14.5	0.2
80°-90°	4.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6202.4	69.6
0°-40°	8166.3	91.7
0°-60°	8857.9	99.5
0°-90°	8906.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8906.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8769	
5°	8743	844
15°	8790	2436
25°	6470	2922
35°	3163	1964
45°	654	588
55°	107	104
65°	25	29
75°	12	14
85°	4	5
90°	0	



TEST NUMBER: P774766

CATALOG NUMBER: LD6D95BD010-EU6DR6570959035-6LBSQW1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8769.0
2.5°	8806.4
5°	8742.9
7.5°	8875.0
10°	8947.2
12.5°	8929.8
15°	8790.2
17.5°	8448.8
20°	7873.1
22.5°	7195.2
25°	6469.9
27.5°	5651.2
30°	4732.8
32.5°	3900.4
35°	3162.7
37.5°	2433.7
40°	1745.8
42.5°	1140.2
45°	654.2
47.5°	346.4
50°	215.6
52.5°	149.5
55°	107.2
57.5°	77.3
60°	53.6
62.5°	34.9
65°	24.9
67.5°	22.4
70°	21.2
72.5°	16.2
75°	12.5
77.5°	11.2
80°	8.7
82.5°	6.2
85°	3.7
87.5°	2.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)